

# Test Report

No. : CE/2007/24798C

Date : 2007/05/14

Page : 1 of 3

BOURNS. INC.  
1200 COLUMBIA AVE. RIVERSIDE, CA 92507, USA



The following sample(s) was/were submitted and identified by/on behalf of the client as :


Sample Description : SMD DIODES  
Style/Item No. : CD1206, CD1005, CD0603, CD1607 SERIES  
Sample Receiving Date : 2007/02/27  
Testing Period : 2007/02/27 TO 2007/03/06

=====  
**Test Requested** : In accordance with the RoHS Directive 2002/95/EC, and its amendment directives.

**Test Method** : With reference to IEC 62321, Ed.1 111/54/CDV  
Procedures for the Determination of Levels of Regulated Substances in  
Electrotechnical Products.

- (1) Determination of Cadmium by ICP-AES.
- (2) Determination of Lead by ICP-AES.
- (3) Determination of Mercury by ICP-AES.
- (4) Determination of Hexavalent Chromium for non-metallic samples by UV/Vis Spectrometry.
- (5) Determination of PBB and PBDE by GC/MS.

**Test Result(s)** : Please refer to next page(s).

  
Daniel Yeh, M.R. / Operation Manager  
Signed for and on behalf of  
SGS TAIWAN LTD.

# Test Report

No. : CE/2007/24798C

Date : 2007/05/14

Page : 2 of 3

BOURNS. INC.

1200 COLUMBIA AVE. RIVERSIDE, CA 92507, USA



Test results by chemical method (Unit: mg/kg)

Test Item (s):	Method (Refer to)	Result	MDL
		No.1	
Cadmium (Cd)	(1)	n.d.	2
Lead (Pb)	(2)	8	2
Mercury (Hg)	(3)	n.d.	2
Hexavalent Chromium Cr(VI) by alkaline extraction	(4)	n.d.	2
<b>Sum of PBBs</b>	(5)	n.d.	-
Monobromobiphenyl		n.d.	5
Dibromobiphenyl		n.d.	5
Tribromobiphenyl		n.d.	5
Tetrabromobiphenyl		n.d.	5
Pentabromobiphenyl		n.d.	5
Hexabromobiphenyl		n.d.	5
Heptabromobiphenyl		n.d.	5
Octabromobiphenyl		n.d.	5
Nonabromobiphenyl		n.d.	5
Decabromobiphenyl		n.d.	5
<b>Sum of PBDEs (Mono to Nona) (Note 4)</b>		n.d.	-
Monobromobiphenyl ether		n.d.	5
Dibromobiphenyl ether		n.d.	5
Tribromobiphenyl ether		n.d.	5
Tetrabromobiphenyl ether		n.d.	5
Pentabromobiphenyl ether		n.d.	5
Hexabromobiphenyl ether		n.d.	5
Heptabromobiphenyl ether		n.d.	5
Octabromobiphenyl ether		n.d.	5
Nonabromobiphenyl ether		n.d.	5
Decabromobiphenyl ether		n.d.	5
<b>Sum of PBDEs (Mono to Deca)</b>		n.d.	-

## TEST PART DESCRIPTION:

NO.1 : MIXED ALL PARTS (4 STYLES)

- Note :
1. mg/kg = ppm
  2. n.d. = Not Detected
  3. MDL = Method Detection Limit
  4. According to 2005/717/EC DecaBDE is exempt.
  5. "-" = Not Regulated

## Test Report

No. : CE/2007/24798C

Date : 2007/05/14

Page : 3 of 3

BOURNS. INC.  
1200 COLUMBIA AVE. RIVERSIDE, CA 92507, USA



\*\* End of Report \*\*