



Test Report

BOURNS ELECTRONICS (TAIWAN) LTD.
1, KUNG 6TH ROAD, INDUSTRIAL ZONE II, LIN-KOU
SHIANG, TAIPEI HSIEN, TAIWAN


Report No. : CE/2005/41063A
Date : 2005/04/15
Page : 1 of 4

The following merchandise was (were) submitted and identified by the client as :

Type of Product : MULTIFUSE
Style/Item No : MF-RX/250,MF-RX/250U FAMILY MODEL
Buyer/Order No : BOURNS
Sample Received : 2005/03/17 & 2005/04/07
Testing Date : 2005/03/17 TO 2005/03/24 &
2005/04/07 TO 2005/04/15

=====
Test Result : - Please see the next page -

This report is combined with report of CE/2005/33806


Daniel Yeh, M.R. / Operation Manager
Signed for and on behalf of
SGS TAIWAN LTD.



Test Report

BOURNS ELECTRONICS (TAIWAN) LTD.
 1, KUNG 6TH ROAD, INDUSTRIAL ZONE II, LIN-KOU
 SHIANG, TAIPEI HSIEN, TAIWAN

Report No. : CE/2005/41063A
 Date : 2005/04/15
 Page : 2 of 4

Test Result

PART NAME NO.1 : MIXED ALL PARTS (PLEASE REFER TO THE PHOTO ATTACHED)

| Test Item (s): | Unit | Method | MDL | Result |
|--|------|---|--------|--------|
| | | | | No.1 |
| Monobromobiphenyl | % | With reference to USEPA3540C or USEPA3550C. Analysis was performed by HPLC/DAD, LC/MS or GC/MS. (prohibited by 2002/95/EC (RoHS), 83/264/EEC, and 76/769/EEC) | 0.0005 | N.D. |
| Dibromobiphenyl | % | | 0.0005 | N.D. |
| Tribromobiphenyl | % | | 0.0005 | N.D. |
| Tetrabromobiphenyl | % | | 0.0005 | N.D. |
| Pentabromobiphenyl | % | | 0.0005 | N.D. |
| Hexabromobiphenyl | % | | 0.0005 | N.D. |
| Heptabromobiphenyl | % | | 0.0005 | N.D. |
| Octabromobiphenyl | % | | 0.0005 | N.D. |
| Nonabromobiphenyl | % | | 0.0005 | N.D. |
| Decabromobiphenyl | % | | 0.0005 | N.D. |
| Total PBBs(Polybrominated) | % | - | N.D. | |
| Monobromobiphenyl ether | % | With reference to USEPA3540C or USEPA3550C. Analysis was performed by HPLC/DAD, LC/MS or GC/MS. (prohibited by 2002/95/EC (RoHS), 83/264/EEC, and 76/769/EEC) | 0.0005 | N.D. |
| Dibromobiphenyl ether | % | | 0.0005 | N.D. |
| Tribromobiphenyl ether | % | | 0.0005 | N.D. |
| Tetrabromobiphenyl ether | % | | 0.0005 | N.D. |
| Pentabromobiphenyl ether | % | | 0.0005 | N.D. |
| Hexabromobiphenyl ether | % | | 0.0005 | N.D. |
| Heptabromobiphenyl ether | % | | 0.0005 | N.D. |
| Octabromobiphenyl ether | % | | 0.0005 | N.D. |
| Nonabromobiphenyl ether | % | | 0.0005 | N.D. |
| Decabromobiphenyl ether | % | | 0.0005 | N.D. |
| Total PBBEs(PBDEs)(Polybrominated biphenyl ethers)/Sum of above | % | - | N.D. | |



Test Report

BOURNS ELECTRONICS (TAIWAN) LTD.
1, KUNG 6TH ROAD, INDUSTRIAL ZONE II, LIN-KOU
SHIANG, TAIPEI HSIEN, TAIWAN

Report No. : CE/2005/41063A
Date : 2005/04/15
Page : 3 of 4

| Test Item (s): | Unit | Method | MDL | Result |
|--------------------|------|--|-----|--------|
| | | | | No.1 |
| Chromium VI (Cr+6) | ppm | As per US EPA 7196A and US EPA 3060A. | 2 | N.D. |
| Cadmium (Cd) | ppm | ICP-AES after as per EN 1122, method B:2001 or other acid digestion. | 2 | N.D. |
| Mercury (Hg) | ppm | ICP-AES after as per US EPA 3052 or other acid digestion. | 2 | N.D. |
| Lead (Pb) | ppm | ICP-AES after reference to US EPA 3050B or other acid digestion. | 2 | 38.2 |

- NOTE: (1) N.D. = Not detected (<MDL)
(2) ppm = mg/kg
(3) MDL = Method Detection Limit
(4) " --- " = Not Applicable
(5) " - " = No Regulation

Test Report

BOURNS ELECTRONICS (TAIWAN) LTD.
1, KUNG 6TH ROAD, INDUSTRIAL ZONE II, LIN-KOU
SHIANG, TAIPEI HSIEN, TAIWAN

Report No. : CE/2005/41063A
Date : 2005/04/15
Page : 4 of 4

