

Features

- RoHS compliant*
- Protects four lines

Max.

-55 to +150

-55 to +150

- Unidirectional and bidirectional configurations
- ESD protection: 30 kV max.

Applications

- Audio/video inputs
- RS-232, RS-422 and RS-423 data lines
- Portable electronics
- Medical sensors

CDNBS08-T03~T36C - TVS Diode Array Series

General Information

Parameter


Operating Temperature

Storage Temperature

The markets of portable communications, computing and video equipment are challenging the semiconductor industry to develop increasingly smaller electronic components.

Bourns offers Steering Diode/Transient Voltage Suppressor Array diodes for surge and ESD protection applications in an eight lead narrow body SOIC package size format. TheTransient Voltage Suppressor Array series offer a choice of voltage types ranging from 3 V to 36 V in unidirectional and bidirectional configurations. Bourns® Chip Diodes conform to JEDEC standards, are easy to handle on standard pick and place equipment and their flat configuration minimizes roll away.

The Bourns $^{\circ}$ device will meet IEC 61000-4-2 (ESD), IEC 61000-4-4 (EFT) and IEC 61000-4-5 (Surge) requirements.



Unit

°C

°C

Additional Information

Click these links for more information:





WARNING Cancer and Reproductive Harm www.P65Warnings.ca.gov

*RoHS Directive 2015/863, Mar 31, 2015 and Annex. Specifications are subject to change without notice. Users should verify actual device performance in their specific applications.

The products described herein and this document are subject to specific legal disclaimers as set forth on the last page of this document, and at

www.bourns.com/docs/legal/disclaimer.pdf

Electrical Characteristics (@ T_A = 25 °C Unless Otherwise Noted)

Thermal Characteristics (@ T_A = 25 °C Unless Otherwise Noted)

Symbol

TJ

T_{STG}

	CDNBS08-															
Parameter	Symbol	Uni- T03	Bi- T03C	Uni- T05	Bi- T05C	Uni- T08	Bi- T08C	Uni- T12	Bi- T12C	Uni- T15	Bi- T15C	Uni- T24	Bi- T24C	Uni- T36	Bi- T36C	Unit
Min. Breakdown Voltage @ 1 mA	V _{BR}	3.3		6.0		8.5		13.3		16.7		26.7		40.0		V
Working Peak Voltage	V _{WM}	3.0		5.0		8.0		12.0		15.0		24.0		36.0		V
Max. Clamping Voltage $V_C @ I_P = 1 A^1$	V _C	8.0		9.8		13.4		19.0		24.0		43.0		51.0		v
Typ. Clamping Voltage @ 8/20 μ s V _C @ I _{PP} ¹	V _C	10.9 V @ 43 A		13.5 V @ 42 A		16.9 V @ 34 A		25.9 V @ 21 A		30.0 V @ 17 A		49.0 V @ 12 A		76.8 V @ 9 A		v
Max. Leakage Current @ V _{WM}	I _D	125		20		10		1		1		1			1	μA
Max. Cap. Bidirectional @ 0 V, 1 MHz	C _{J(SD)}	450		308		300		105 80		0	50		4	5	pF	
ESD Protection per IEC 61000-4-2 Contact - Min. Contact - Max. Air - Min. Air - Max.	ESD	±8 ±30 ±15 ±30								kV						
Peak Pulse Power ($t_p = 8/20 \ \mu s$) ²	P _{PP}	500							W							
Forward Voltage @ 100 mA, $300 \ \mu s$ - Square Wave ³	V _F		1.5										v			

Notes:

1. See Pulse Wave Form.

2. See Peak Pulse Power vs. Pulse Time.

3. Only applies to unidirectional devices.

4. Part numbers with a "C" suffix are bidirectional devices, i.e. CDNBS08-T03C.


CDNBS08-T03~T36C - TVS Diode Array Series


(INCHES)

BOURNS

Product Dimensions


This is an RoHS compliant molded JEDEC narrow body SO-8 package with 100 % Sn plating on the lead frame. It weighs approximately 15 mg and has a flammability rating of UL 94V-0.





Dimensions					
А	<u>4.80 - 5.00</u> (0.189 - 0.197)				
в	<u>3.81 - 4.00</u> (0.150 - 0.157)				
С	$\frac{5.80 - 6.20}{(0.228 \pm 0.244)}$				
D	<u>0.36 - 0.51</u> (0.014 - 0.020)				
E	<u>1.35 - 1.75</u> (0.053 - 0.069)				
F	<u>0.102 - 0.203</u> (0.004 - 0.008)				
G	<u>0.25 - 0.50</u> (0.010 - 0.020)				
н	<u>0.51 - 1.12</u> (0.020 - 0.044)				
I	<u>0.190 - 0.229</u> (0.0075 - 0.0090)				
J	<u>4.60 - 5.21</u> (0.181 - 0.205)				
к	<u>0.28 - 0.79</u> (0.011 - 0.031)				
L	<u>1.27</u> (0.050)				

Recommended Footprint



Dimensions					
A	<u>1.143 - 1.397</u> (0.045 - 0.065)				
В	<u>0.635 - 0.889</u> (0.025 - 0.035)				
С	<u>6.223</u> (0.245) Min.				
D	<u>3.937 - 4.191</u> (0.155 - 0.165)				
E	<u>1.016 - 1.27</u> (0.040 - 0.050)				

MM DIMENSIONS: (INCHES)

Typical Part Marking

CDNBS08-T03SDL CDNBS08-T03CSDM CDNBS08-T05SDA CDNBS08-T05CSDB CDNBS08-T08SDJ CDNBS08-T08CSDK CDNBS08-T12.SDC	CDNBS08-T12CSDD CDNBS08-T15SDE CDNBS08-T15CSDF CDNBS08-T24SDG CDNBS08-T24CSDH CDNBS08-T36SDP
CDNBS08-T12SDC	CDNBS08-T36C SDP

How to Order

	CD NBS08 - T 03 C
Common Code Chip Diode	
Package NBS08 = Narrow Body SOIC8 Package	
ModelT = Transient Voltage Suppressor	
Working Peak Voltage 03 = 3 V _{RWM} (Volts)	
Suffix	

C = Bidirectional Diode

Specifications are subject to change without notice.


Users should verify actual device performance in their specific applications.


The products described herein and this document are subject to specific legal disclaimers as set forth on the last page of this document, and at www.bourns.com/docs/legal/disclaimer.pdf.

CDNBS08-T03~T36C - TVS Diode Array Series

BOURNS®

Performance Graphs







Device Pinout

Pin	Function
1	I/O 1
2	I/O 2
3	I/O 3
4	I/O 4
5	GND
6	GND
7	GND
8	GND

Pulse Waveform



Power Derating Curve



Specifications are subject to change without notice.


Users should verify actual device performance in their specific applications. The products described herein and this document are subject to specific legal disclaimers as set forth on the last page of this document, and at <u>www.bourns.com/docs/legal/disclaimer.pdf</u>.


CDNBS08-T03~T36C - TVS Diode Array Series

BOURNS

Packaging Information

The product is packaged in tape and reel format per EIA-481 standard.





DIMENSIONS: $\frac{MM}{(INCHES)}$

Γ		
Item	Symbol	NSOIC 8L
Carrier Width	А	$\frac{6.7 \pm 0.10}{(0.264 \pm 0.004)}$
Carrier Length	В	$\frac{5.5 \pm 0.10}{(0.217 \pm 0.004)}$
Carrier Depth	С	$\frac{2.10 \pm 0.10}{(0.083 \pm 0.004)}$
Sprocket Hole	d	$\frac{1.55 \pm 0.05}{(0.061 \pm 0.002)}$
Reel Outside Diameter	D	<u>330</u> (12.992)
Reel Inner Diameter	D ₁	<u>80.0</u> (3.1500) MIN.
Feed Hole Diameter	D ₂	$\frac{13.0 \pm 0.20}{(0.512 \pm 0.008)}$
Sprocket Hole Position	E	$\frac{1.75 \pm 0.10}{(0.069 \pm 0.004)}$
Punch Hole Position	F	$\frac{3.50 \pm 0.05}{(0.138 \pm 0.002)}$
Punch Hole Pitch	Р	$\frac{8.00 \pm 0.10}{(0.315 \pm 0.004)}$
Sprocket Hole Pitch	P ₀	$\frac{4.00 \pm 0.10}{(0.157 \pm 0.004)}$
Embossment Center	P ₁	$\frac{2.00 \pm 0.05}{(0.079 \pm 0.002)}$
Overall Tape Thickness	т	$\frac{0.20 \pm 0.10}{(0.008 \pm 0.004)}$
Tape Width	w	$\frac{12.00 \pm 0.20}{(0.472 \pm 0.008)}$
Reel Width	W ₁	<u>18.4</u> (0.724) MAX.
Quantity per Reel		2500

BOURNS

Asia-Pacific: Tel: +886-2 2562-4117 Email: asiacus@bourns.com EMEA: Tel: +36 88 885 877 Email: eurocus@bourns.com The Americas: Tel: +1-951 781-5500 Email: americus@bourns.com www.bourns.com

REV. 08/19

Specifications are subject to change without notice. Users should verify actual device performance in their specific applications. The products described herein and this document are subject to specific legal disclaimers as set forth on the last page of this document, and at www.bourns.com/docs/legal/disclaimer.pdf.

Legal Disclaimer Notice

This legal disclaimer applies to purchasers and users of Bourns[®] products manufactured by or on behalf of Bourns, Inc. and its affiliates (collectively, "Bourns").

Unless otherwise expressly indicated in writing, Bourns[®] products and data sheets relating thereto are subject to change without notice. Users should check for and obtain the latest relevant information and verify that such information is current and complete before placing orders for Bourns[®] products.

The characteristics and parameters of a Bourns[®] product set forth in its data sheet are based on laboratory conditions, and statements regarding the suitability of products for certain types of applications are based on Bourns' knowledge of typical requirements in generic applications. The characteristics and parameters of a Bourns[®] product in a user application may vary from the data sheet characteristics and parameters due to (i) the combination of the Bourns[®] product with other components in the user's application, or (ii) the environment of the user application itself. The characteristics and parameters of a Bourns[®] product also can and do vary in different applications and actual performance may vary over time. Users should always verify the actual performance of the Bourns[®] product in their specific devices and applications, and make their own independent judgments regarding the amount of additional test margin to design into their device or application to compensate for differences between laboratory and real world conditions.

Unless Bourns has explicitly designated an individual Bourns[®] product as meeting the requirements of a particular industry standard (e.g., ISO/TS 16949) or a particular qualification (e.g., UL listed or recognized), Bourns is not responsible for any failure of an individual Bourns[®] product to meet the requirements of such industry standard or particular qualification. Users of Bourns[®] products are responsible for ensuring compliance with safety-related requirements and standards applicable to their devices or applications.

Bourns[®] products are not recommended, authorized or intended for use in nuclear, lifesaving, life-critical or life-sustaining applications, nor in any other applications where failure or malfunction may result in personal injury, death, or severe property or environmental damage. Unless expressly and specifically approved in writing by two authorized Bourns representatives on a case-by-case basis, use of any Bourns[®] products in such unauthorized applications might not be safe and thus is at the user's sole risk. Life-critical applications include devices identified by the U.S. Food and Drug Administration as Class III devices and generally equivalent classifications outside of the United States.

Bourns expressly identifies those Bourns[®] standard products that are suitable for use in automotive applications on such products' data sheets in the section entitled "Applications." Unless expressly and specifically approved in writing by two authorized Bourns representatives on a case-by-case basis, use of any other Bourns[®] standard products in an automotive application might not be safe and thus is not recommended, authorized or intended and is at the user's sole risk. If Bourns expressly identifies a sub-category of automotive application in the data sheet for its standard products (such as infotainment or lighting), such identification means that Bourns has reviewed its standard product and has determined that if such Bourns[®] standard product is considered for potential use in automotive applications, it should only be used in such sub-category of automotive applications, it should only be used in such sub-category of automotive applications product in the data sheet as compliant with the AEC-Q standard or "automotive grade" does not by itself mean that Bourns has approved such product for use in an automotive application.

Bourns[®] standard products are not tested to comply with United States Federal Aviation Administration standards generally or any other generally equivalent governmental organization standard applicable to products designed or manufactured for use in aircraft or space applications. Bourns expressly identifies Bourns[®] standard products that are suitable for use in aircraft or space applications on such products' data sheets in the section entitled "Applications." Unless expressly and specifically approved in writing by two authorized Bourns representatives on a case-by-case basis, use of any other Bourns[®] standard product in an aircraft or space application might not be safe and thus is not recommended, authorized or intended and is at the user's sole risk.

The use and level of testing applicable to Bourns[®] custom products shall be negotiated on a case-by-case basis by Bourns and the user for which such Bourns[®] custom products are specially designed. Absent a written agreement between Bourns and the user regarding the use and level of such testing, the above provisions applicable to Bourns[®] standard products shall also apply to such Bourns[®] custom products.

Users shall not sell, transfer, export or re-export any Bourns[®] products or technology for use in activities which involve the design, development, production, use or stockpiling of nuclear, chemical or biological weapons or missiles, nor shall they use Bourns[®] products or technology in any facility which engages in activities relating to such devices. The foregoing restrictions apply to all uses and applications that violate national or international prohibitions, including embargos or international regulations. Further, Bourns[®] products and Bourns technology and technical data may not under any circumstance be exported or re-exported to countries subject to international sanctions or embargoes. Bourns[®] products may not, without prior authorization from Bourns and/or the U.S. Government, be resold, transferred, or re-exported to any party not eligible to receive U.S. commodities, software, and technical data.

To the maximum extent permitted by applicable law, Bourns disclaims (i) any and all liability for special, punitive, consequential, incidental or indirect damages or lost revenues or lost profits, and (ii) any and all implied warranties, including implied warranties of fitness for particular purpose, non-infringement and merchantability.

For your convenience, copies of this Legal Disclaimer Notice with German, Spanish, Japanese, Traditional Chinese and Simplified Chinese bilingual versions are available at:

Web Page: <u>http://www.bourns.com/legal/disclaimers-terms-and-policies</u> PDF: http://www.bourns.com/docs/Legal/disclaimer.pdf