



**\*RoHS COMPLIANT & \*\*HALOGEN FREE**

### Features

- Designed to UL 248-13 and IEC 60269-4 semiconductor fuse standards
- 500 VDC/690 VAC and 32-100 A ratings available
- Up to 100 kA interrupting rating
- Compact size: 17.5 mm dia. x 46 mm L
- Bolt-down mounting type
- RoHS compliant\* and halogen free\*\*

### Applications

- Energy Storage Systems
- Battery pack protection
- Battery Disconnect Unit (BDU)
- Battery module protection

### Sustainability

- Small size reduces material use
- ISO 14001, low impact energy

### Product Overview



Bourns® PF-SRC50E Series POWrFuse™ High-Power Fuses feature high-power industrial fuse links designed to meet UL 248-13 and IEC 60269-4 (aR Class) semiconductor standards.

The PF-SRC50E Series is engineered to protect semiconductor devices against overcurrent conditions. Housed in a compact 17.5 mm diameter by 46 mm length, this bolt-down mounting series is ideal for use in power inverters, converters, rectifiers, AC/DC drives, uninterruptible power supplies (UPS) and reduced voltage motor starters.

### Electrical Characteristics

Model	Rated Current (A)	Rated Voltage	Interrupting Rating	$i^2t$ (A <sup>2</sup> S)***		Max. Power Loss (W)****	Agency Recognition
				Pre-arcing	Cleaning		
PF-SRC50E32B1	32	500 VDC 690 VAC	50 kA @ 500 VDC 100 kA @ 690 VAC	44	320	7.6	  
PF-SRC50E40B1	40			53	400	10.0	
PF-SRC50E50B1	50			120	900	11.6	
PF-SRC50E63B1	63			210	1600	12.5	
PF-SRC50E80B1	80			330	2400	18.2	
PF-SRC50E100B1	100			480	3500	26.7	

\*\*\* The value is measured at maximum breaking capacity (DC); the minimum breaking capacity = 500 % of rated current.

\*\*\*\* Measured at 100 % of rated current.

### Environmental Characteristics

Operating Temperature Range..... -40 °C to +85 °C  
Storage Conditions ..... 10~30 °C; 30~70 % RH

### Contact Information

<a href="http://www.bourns.com">www.bourns.com</a>	Phone	Email
Asia-Pacific	+886-2 2562-4117	<a href="mailto:asiacus@bourns.com">asiacus@bourns.com</a>
Europe	+36 88 885 877	<a href="mailto:eurocus@bourns.com">eurocus@bourns.com</a>
Mexico	+52 614 478 0400	<a href="mailto:mexicus@bourns.com">mexicus@bourns.com</a>
The Americas	+1-951 781-5500	<a href="mailto:americus@bourns.com">americus@bourns.com</a>

### How to Order

**PF - SRC 50E 100 B1**

POWrFuse™ Product Designator \_\_\_\_\_

Series Name \_\_\_\_\_

Rated Voltage \_\_\_\_\_  
50E = 500 VDC

Rated Current \_\_\_\_\_  
30 ~ 100 = 32 A ~ 100 A

Mounting Type \_\_\_\_\_  
B1 = Bolt-Down, Type 1

\* RoHS Directive 2015/863, Mar 31, 2015 and Annex.

\*\* Bourns considers a product to be "halogen free" if (a) the Bromine (Br) content is 900 ppm or less; (b) the Chlorine (Cl) content is 900 ppm or less; and (c) the total Bromine (Br) and Chlorine (Cl) content is 1500 ppm or less.

Specifications are subject to change without notice.

Users should verify actual device performance in their specific applications.


The products described herein and this document are subject to specific legal disclaimers as set forth on the last page of this document, and at [www.bourns.com/docs/legal/disclaimer.pdf](http://www.bourns.com/docs/legal/disclaimer.pdf).




**\*RoHS COMPLIANT & \*\*HALOGEN FREE**

**Product Dimensions**


**Bolt-down (B1 Type)**




**Power Dissipation Curve (for Reference Only)**



**Average Pre-Arcing Time vs. Current Curves (for Reference Only)**




**Cut-off Current Characteristic Curves (for Reference Only)**





\*RoHS COMPLIANT  
&  
\*\*HALOGEN FREE




#### Current Rating Thermal Derating Curve



#### Recommended Mounting Torque and Bolt Sizes

Mounting Torque	Bolt Size
6 ± 1 Nm	M6

#### Typical Part Marking

Current Rating (A)	Note	Ink Color	Marking
32	32	Black	<b>BOURNS®</b> PF-SRC50E Note A 690VAC 100kA 500VDC 50kA aR   
40	40		
50	50		
63	63		
80	80		
100	100		

#### Packaging

Series	Quantity	
	Pallet	Outer Box
PF-SRC50E	40 pcs.	240 pcs.

REV. 03/26  
 Specifications are subject to change without notice.  
 Users should verify actual device performance in their specific applications.

The products described herein and this document are subject to specific legal disclaimers as set forth on the last page of this document, and at [www.bourns.com/docs/legal/disclaimer.pdf](http://www.bourns.com/docs/legal/disclaimer.pdf).

This legal disclaimer applies to purchasers and users of Bourns® products manufactured by or on behalf of Bourns, Inc. and its affiliates (collectively, "Bourns").

Unless otherwise expressly indicated in writing, Bourns® products and data sheets relating thereto are subject to change without notice. Users should check for and obtain the latest relevant information and verify that such information is current and complete before placing orders for Bourns® products.

The characteristics and parameters of a Bourns® product set forth in its data sheet are based on laboratory conditions, and statements regarding the suitability of products for certain "typical" applications are based on Bourns' knowledge of typical requirements in generic applications. Bourns assumes that "typical" applications include failsafe/backup features to address critical risks to users and are designed to allow rework of Bourns® product to avoid scrap of a device solely due to malfunctioning Bourns® product. The characteristics and parameters of a Bourns® product in a user application may vary from the data sheet characteristics and parameters due to (i) the combination of the Bourns® product with other components in the user's application, or (ii) the environment of the user application itself. The characteristics and parameters of a Bourns® product also can and do vary in different applications and actual performance may vary over time. Thus, users should always verify the actual performance of the Bourns® product in their specific devices and applications and make their own independent judgments regarding the suitability of Bourns® product and the amount of additional test margin to design into their device or application to compensate for differences between laboratory and real-world conditions.

Unless Bourns has explicitly designated an individual Bourns® product as meeting the requirements of a particular industry standard (e.g., IATF 16949) or a particular qualification (e.g., UL listed or recognized), Bourns is not responsible for any failure of an individual Bourns® product to meet the requirements of such industry standard or particular qualification even if such industry standard or qualification is a "state of art". Users of Bourns® products are responsible for ensuring compliance with safety-related requirements and standards applicable to their devices or applications.

Bourns® products are not recommended, authorized or intended for use in applications where failure or malfunction may result in personal injury, death, or severe property or environmental damage, such as without limitation nuclear, life-critical medical and certain automotive and aviation applications. Except as set forth in the bullet points below or unless expressly and specifically approved in writing on a case-by-case basis by an authorized Bourns' representative, use of any Bourns® products in such unauthorized high-risk applications is at the user's sole risk.

- Bourns considers implantable/invasive devices and devices/procedures designed as life-supporting or life-sustaining by the U.S. Food and Drug Administration or equivalent organizations outside of the United States as "life-critical" medical applications. Bourns expressly identifies those Bourns® standard products that are suitable for use in typical medical applications that are not life-critical in its publication entitled "Bourns Medical Grade Component Guide."
- Bourns expressly identifies those Bourns® standard products that are suitable for use in typical automotive applications associated with any Automate Safety Integrity Level (ASIL) in its publication entitled "Bourns Automotive Grade Component Guide." Bourns' designation of Bourns® product as compliant with the AEC-Q standard does not by itself mean that Bourns has approved such product for use in an automotive application.
- Bourns expressly identifies Bourns® standard products that are suitable for use in the typical aviation applications/systems requiring System Design Assurance Level (RTCA DO-254 DAL) of C, D or E in its publication entitled "Bourns Civilian Aerospace/Aviation Grade Component Guide." Bourns does not test its products for compliance with United States Federal Aviation Administration standards or any other generally equivalent governmental organization standard applicable to products designed or manufactured for use in aviation applications. Use of Bourns® standard components in aviation applications associated with RTCA DO-254 DAL A or B without proper approval noted above shall be at the user's sole risk.
- Bourns will review and authorize on a case-by-case basis the use of Bourns® standard products which are at least AEC-Q compliant in space-related civil applications (rockets, satellites) with a negotiated cross-waiver and indemnity agreement.

The use and level of testing applicable to Bourns® custom products shall be negotiated on a case-by-case basis by Bourns and the user for which such Bourns® custom products are specially designed. Absent a written agreement between Bourns and the user regarding the use and level of such testing, the above provisions applicable to Bourns® standard products shall also apply to such Bourns® custom products.

Use of Bourns® products or Bourns' technology in military/defense applications must be reviewed with Bourns for compliance with applicable export control laws and embargoes. Users shall not sell, transfer, export or re-export (which includes transfers within a country) any Bourns® products or technology or technical data for use in activities which involve the design, development, production, use or stockpiling of nuclear, chemical or biological weapons or missiles, nor shall they use Bourns® products or technology or technical data in any facility which engages in activities relating to such devices. Further, Bourns® products and Bourns' technology and technical data may not under any circumstance be exported or re-exported to countries subject to international sanctions or embargoes. Bourns® products and technology may not, without prior authorization from Bourns and/or the Government of a country where such product/technology is designed and/or manufactured, be resold, transferred, or re-exported (including within the same country) to any party not eligible to receive commodities, software, and technical data originating in such country.

To the maximum extent permitted by applicable law, Bourns disclaims (i) any and all liability for special, punitive, consequential, incidental or indirect damages or lost revenues or lost profits, and (ii) any and all implied warranties (those not based on parameters specified in Bourns' data sheets and/or specifications), including implied warranties of fitness for particular purpose, non-infringement and merchantability.

For your convenience, copies of this Legal Disclaimer Notice with German, Spanish, Japanese, Traditional Chinese and Simplified Chinese bilingual versions are available at:

Web Page: <https://www.bourns.com/legal/disclaimers-terms-and-policies>

PDF: <https://www.bourns.com/docs/Legal/disclaimer.pdf>

K2540 05/26R



**CALIFORNIA WARNING:** Can expose you to lead, a carcinogen and reproductive toxicant.

See [www.P65Warnings.ca.gov](http://www.P65Warnings.ca.gov)