


MATERIAL DECLARATION SHEET



Material Number	1250A-2S series			
Product Line	SPD			
Compliance Date	Oct 2024			
RoHS Compliant	Yes	MSL	1	

NO	Construction Element (subpart)	Homogeneous Materials	Material weight [g]	Homogeneous Material	CASRN	Materials Mass %	Material Mass % of total unit wt.	Subpart mass of total wt • (%)
				Substances	if applicable			
1	Varistor	Ceramic	47.8	Zinc oxide	1314-13-2	99.00%	19.78%	19.98%
				Manganese oxide	1344-43-0	0.25%	0.05%	
				Nickel oxide	1313-99-1	0.25%	0.05%	
				Cobalt oxide	1307-96-6	0.25%	0.05%	
				Bismuth trioxide	1304-76-3	0.25%	0.05%	
	Termination	2	Silver	7440-22-4	100.00%	0.84%	0.84%	
2	Plastic shell	PBT	99.2	Polybutylene terephthalate	63440-93-7	80.00%	33.17%	41.47%
				Glass fiber	65997-17-3	20.00%	8.29%	
3	Spring	Spring	0.6	Iron	7439-89-6	98.00%	0.25%	0.25%
				Manganese	7439-96-5	0.65%	0.00%	
				Carbon	7440-44-0	0.65%	0.00%	
				Silicon	7440-21-3	0.20%	0.00%	
				Misc not to declare	---	0.50%	0.00%	
4	Switch	Brass	1.6	Copper	7440-50-8	65.00%	0.43%	0.43%
				Lead	7439-92-1	0.02%	0.00%	
				Zinc	7440-66-6	34.95%	0.23%	0.60%
				Iron	7439-89-6	0.03%	0.00%	

MATERIAL DECLARATION SHEET



		Plastic shell	1.76	PBT resin (C12H12O4) n	26062-94-2	50.00%	0.37%	0.69%	
				Glass fiber.	65997-17-3	30.00%	0.22%		
				Flame retardant (C 18 H 16 Br 4 O 3) n	68928-70-1	12.00%	0.09%		
				Flame retardant Sb2O3	1309-64-4	8.00%	0.06%		
		Phosphorous copper	0.7	Copper	7440-44-8	95.20%	0.28%		
				Tin	7440-31-5	4.80%	0.01%		
		Silver plated	0.08	Silver	7440-22-4	90.00%	0.03%		
				Nickel	7440-02-0	10.00%	0.00%		
		Nylon	0.26	PA66	32131-17-2	50.00%	0.05%		0.11%
				Glass fiber	65997-17-3	30.00%	0.03%		
				Brominated polystyrene	88497-56-7	19.50%	0.02%		
				Antioxidant	23128-74-7	0.50%	0.00%		
		SUS304	1.12	Iron	7439-89-6	73.00%	0.34%		0.47%
Chromium	7440-47-3			18.00%	0.08%				
Nickel	7440-02-0			9.00%	0.04%				
5	Electrode	Copper part	59.4	Copper	7440-50-8	91.55%	22.73%	24.83%	
				Tin	7440-31-5	8.00%	1.99%		
				Zinc	31396-84-6	0.30%	0.07%		
				Phosphorus	7723-14-0	0.15%	0.04%		
6	Low-temperature alloys	Alloys Solder	1	Tin	7440-31-5	42.00%	0.18%	0.42%	
				Bismuth	7440-69-9	58.00%	0.24%		
7	Potting adhesive	Potting adhesive	10	Polydimethylsiloxane	68083-19-2	60.00%	2.51%	4.18%	
				Polymethylhydrosiloxane	63148-57-2	5.00%	0.21%		
				Alumina	1344-28-1	24.00%	1.00%		
				Aluminum hydroxide	21645-51-2	10.00%	0.42%		
				Platinum	68478-92-2	0.20%	0.01%		

MATERIAL DECLARATION SHEET



				Carbon black	1333-86-4	0.80%	0.03%	
8	Screw	Carbon steel	13.6	Carbon	7440-44-0	0.19%	0.01%	5.69%
				Manganese	7439-96-5	0.78%	0.04%	
				Phosphorus	7723-14-0	0.02%	0.00%	
				Sulfur	7704-34-9	0.01%	0.00%	
				Silicon	7440-21-3	0.04%	0.00%	
				Aluminum	7429-90-5	0.04%	0.00%	
				Iron	7439-89-6	98.91%	5.62%	
				Other additives	67763-03-5	5.00%	0.00%	
9	Ink Printing	Ink	0.1	Epoxy Resins	61788-97-4	60.00%	0.03%	0.04%
				Titanium dioxide powder, color powder	1333-86-4	35.00%	0.01%	
				Other additives	67763-03-5	5.00%	0.00%	
Total			239.22					

This Document was updated: Oct 2024

Important remarks:

1. It is the responsibility of the user to verify they are accessing the latest version.