


MATERIAL DECLARATION



Material Number	3306W (1KΩ ≤ RC)			
Product Line	Trimmer			
Compliance Date	RoHS Directive 2015/863 Mar. 31, 2015 and Annex. 8-26-2004 Updated : 11/26/2024			
RoHS Compliant	Yes	MSL	1	

NO	Construction Element(subpart)	Homogeneous Material	Material weight [g]	Homogeneous Material\ Substances	CASRN if applicable	Materials Mass %	Mass % of total unit wt. Material	Subpart mass of total wt. (%)
1	SUBSTRATE	ALUMINA	0.13	Magnesium oxide	1309-48-4	2	0.741	37.068
				Silica, Crystalline	14808-60-7	3	1.112	
				Aluminum oxide	1344-28-1	95	35.214	
2	ELECTRODE	GLASS Ag-Pd	0.001	Copper (metallic)	7440-50-8	0.63	0.002	0.285
				Palladium	7440-05-3	3.8	0.011	
				Silver	7440-22-4	92	0.262	
				Glass without declarable substances	-	1	0.003	
				Misc., not to declare	-	2.57	0.007	
3	RESISTANCE ELEMENT	METAL GLAZED RESISTORS	0.0012	Dicopper oxide	1317-39-1	0.17	0.001	0.342
				Silver	7440-22-4	33.24	0.114	
				Tin oxide	18282-10-5	0.17	0.001	
				Manganese dioxide	1313-13-9	0.7	0.002	
				Ruthenium(IV) oxide	12036-10-1	32.19	0.110	
				Glass without declarable substances	Trade secret	33.53	0.115	
4	MARKING	EPOXY RESIN	0.00001	Organic phosphorus compound ISO 1043-4, not declarable	-	0.08	0.000002	0.003
				Copper phthalocyanine	147-14-8	1.5	0.00004	
				Barium sulfate	7727-43-7	17.1	0.0005	
				Silica, Crystalline	14808-60-7	17.2	0.0005	
				Talc	14807-96-6	1.9	0.00005	
				Siloxane resin	-	7.52	0.0002	

MATERIAL DECLARATION



5	TERMINAL CONNECTOR	SOLDER Sn-3Ag-0.5Cu	0.0015	Epoxy resin	Trade secret	54.7	0.0016	0.428
				Lead	7439-92-1	0.0499	0.0002	
				Antimony	7440-36-0	0.05	0.0002	
				Arsenic, elemental	7440-38-2	0.03	0.0001	
				Bismuth	7440-69-9	0.1	0.0004	
				Copper (metallic)	7440-50-8	0.5	0.002	
				Silver	7440-22-4	3	0.013	
				Tin	7440-31-5	96.2701	0.412	
6	KNOB	PA6	0.081	Plastic:PA6	Trade secret	99	22.865	23.096
				epsilon-Caprolactam	105-60-2	1	0.231	
7	1-3 TERMINALS	STEEL	0.04003	Iron	7439-89-6	99.55	11.363	11.414
				Manganese	7439-96-5	0.3	0.034	
				Carbon	7440-44-0	0.075	0.009	
				Phosphorus	7723-14-0	0.05	0.006	
				Sulphur	7704-34-9	0.025	0.003	
8	1-3 TERMINAL GROUND PLATING	GNi	0.000227	Nickel	7440-02-0	99.75	0.065	0.065
				Misc., not to declare	-	0.25	0.0002	
9	1-3 TERMINAL PLATING	Sn	0.000743	Tin	7440-31-5	99.75	0.211	0.212
				Misc., not to declare	-	0.25	0.001	
10	2 TERMINAL	STEEL	0.068345	Iron	7439-89-6	99.695	19.428	19.488
				Manganese	7439-96-5	0.225	0.044	
				Carbon	7440-44-0	0.05	0.010	
				Phosphorus	7723-14-0	0.015	0.003	
				Sulphur	7704-34-9	0.015	0.003	
11	2 TERMINAL GROUND PLATING	Ni	0.000387	Nickel	7440-02-0	99.75	0.110	0.110
				Misc., not to declare	-	0.25	0.0003	
12	2 TERMINAL PLATING	Sn	0.001268	Tin	7440-31-5	99.75	0.361	0.362
				Misc., not to declare	-	0.25	0.001	
13	MOVING CONTACT	COPPER ALLOY	0.025	Lead	7439-92-1	0.015	0.001	7.128
				Nickel	7440-02-0	18	1.283	
				Copper (metallic)	7440-50-8	64	4.562	
				Iron	7439-89-6	0.125	0.009	
				Zinc	7440-66-6	17.61	1.255	
				Manganese	7439-96-5	0.25	0.018	

MATERIAL DECLARATION

BOURNS®

Total weight	0.35071
--------------	---------

This Document was updated on:11/26/2024

Important remarks:

1. It is the responsibility of the user to verify they are accessing the latest version.