

TISP4070M3AJ THRU TISP4115M3AJ, TISP4125M3AJ THRU TISP4220M3AJ. TISP4240M3AJ THRU TISP4395M3AJ

BIDIRECTIONAL THYRISTOR OVERVOLTAGE PROTECTORS

TISP4xxxM3AJ Overvoltage Protector Series

4 kV 10/700, 100 A 5/310 ITU-T K.20/21 rating

SMA (DO-214AC) Package 25 % Smaller Placement Area than SMB

Low Differential Capacitance 39 pF

Ion-Implanted Breakdown Region **Precise and Stable Voltage** Low Voltage Overshoot under Surge

Davisa	V _{DRM}	V _(BO)
Device	V	v
'4070	58	70
'4080	65	80
'4095	75	95
'4115	90	115
'4125	100	125
'4145	120	145
'4165	135	165
'4180	145	180
'4200	155	200
'4220	160	220
'4240	180	240
'4250	190	250
'4265	200	265
'4290	220	290
'4300	230	300
'4320	240	320
'4350	275	350
'4360	290	360
'4395	320	395

SMAJ Package (Top View)



MDXXCCE

Device Symbol



Terminals T and R correspond to the alternative line designators of A and B

Rated for International Surge Wave **Shapes**

•		
Wave Shape	Standard	I _{TSP} A
2/10 μs	GR-1089-CORE	300
8/20 μs	IEC 61000-4-5	220
10/160 μs	FCC Part 68	120
10/700 μs	ITU-T K.20/21/45	100
10/560 μs	FCC Part 68	75
10/1000 μs	GR-1089-CORE	50



Additional Information

Click these links for more information:











PRODUCT TECHNICAL LIBRARY

Description

These devices are designed to limit overvoltages on the telephone line. Overvoltages are normally caused by a.c. power system or lightning flash disturbances which are induced or conducted on to the telephone line. A single device provides 2-point protection and is typically used for the protection of 2-wire telecommunication equipment (e.g. between the Ring and Tip wires for telephones and modems). Combinations of devices can be used for multi-point protection (e.g. 3-point protection between Ring, Tip and Ground).

The protector consists of a symmetrical voltage-triggered bidirectional thyristor. Overvoltages are initially clipped by breakdown clamping until the voltage rises to the breakover level, which causes the device to crowbar into a low-voltage on state. This low-voltage on state causes the current resulting from the overvoltage to be safely diverted through the device. The high crowbar holding current helps prevent d.c. latchup as the diverted current subsides.

The TISP4xxxM3AJ range consists of twenty voltage variants to meet various maximum system voltage levels (58 V to 320 V). They are guaranteed to voltage limit and withstand the listed international lightning surges in both polarities. These medium (M) current protection devices are in a plastic package SMAJ (JEDEC DO-214AC with J-bend leads) and supplied in embossed tape reel pack. For alternative voltage and holding current values, consult the factory. For higher rated impulse currents, the 100 A 10/1000 TISP4xxxH3BJ series in the SMB (JEDEC DO-214AA) package is available.

How to Order

Device	Package	Carrier	Order As
TISP4xxxM3AJ	AJ (J-Bend DO-214AC/SMA)	Embossed Tape Reeled	TISP4xxxM3AJR-S

Insert xxx value corresponding to protection voltages of 070, 080, 095, etc.



WARNING Cancer and Reproductive Harm www.P65Warnings.ca.gov

NOVEMBER 1997 - REVISED MARCH 2023

*RoHS Directive 2015/863, Mar 31, 2015 and Annex.

Specifications are subject to change without notice.

Users should verify actual device performance in their specific applications.

The products described herein and this document are subject to specific legal disclaimers as set forth on the last page of this document, and at www.bourns.com/docs/legal/disclaimer.pdf.

Absolute Maximum Ratings, TA = 25 °C (Unless Otherwise Noted)

Rating	Symbol	Value	Unit
'4070		58	
'4080		65	
'4095		75	
'4115		90	
'4125		100	
'4145		120	
'4165		135	
'4180		145	
'4200		155	
Repetitive peak off-state voltage, (see Note 1) '4220	V_{DRM}	160	V
'4240		180	
'4250		190	
'4265		200	
'4290		220	
'4300		230	
'4320		240	
'4350		275	
'4360		290	
'4395		320	
Non-repetitive peak on-state pulse current (see Notes 2, 3 and 4)			
2/10 μs (GR-1089-CORE, 2/10 μs voltage wave shape)		300	
8/20 μs (IEC 61000-4-5, combination wave generator, 1.2/50 voltage, 8/20 current)	ı	220	
10/160 μs (FCC Part 68, 10/160 μs voltage wave shape)		120	
5/200 μs (VDE 0433, 10/700 μs voltage wave shape)	l	110	_
0.2/310 μs (l3124, 0.5/700 μs voltage wave shape)	I _{TSP}	100	A
5/310 μs (ITU-T K.20/21/45, K.44 10/700 μs voltage wave shape)		100	
5/310 μs (FTZ R12, 10/700 μs voltage wave shape)		100	
10/560 μs (FCC Part 68, 10/560 μs voltage wave shape)		75	
10/1000 µs (GR-1089-CORE, 10/1000 µs voltage wave shape)		50	
Non-repetitive peak on-state current (see Notes 2, 3 and 5)			
20 ms (50 Hz) full sine wave		23	
16.7 ms (60 Hz) full sine wave	I _{TSM}	24	Α
1000 s 50 Hz/60 Hz a.c.		1.6	
Initial rate of rise of on-state current, Exponential current ramp, Maximum ramp value < 100 A	di _T /dt	300	A/s
Junction temperature	TJ	-40 to +150	°C
Storage temperature range	T _{stg}	-65 to +150	°C

- NOTES: 1. See Applications Information and Figure 10 for voltage values at lower temperatures.
 - 2. Initially, the TISP4xxxM3AJ must be in thermal equilibrium with T_J = 25 $^{\circ}C$
 - 3. The surge may be repeated after the TISP4xxxM3AJ returns to its initial conditions.
 - 4. See Applications Information and Figure 11 for current ratings at other temperatures.
 - 5. EIA/JESD51-2 environment and EIA/JESD51-3 PCB with standard footprint dimensions connected with 5 A rated printed wiring track widths. See Figure 9 for the current ratings at other durations. Derate current values at -0.61 %/°C for ambient temperatures above 25 °C.

Electrical Characteristics, TA = 25 °C (Unless Otherwise Noted)

	Parameter	Test Conditions		Min	Тур	Max	Unit
lanı	Repetitive peak off-	$V_D = V_{DRM}$	T _A = 25 °C			±5	μΑ
I _{DRM}	state current	VD - VDRM	$T_A = 85 ^{\circ}C$			±10	μΛ
			'4070			±70	
			'4080			±80	
			'4095			±95	
			'4115			±115	
			'4125			±125	
			'4145			±145	
			'4165			±165	
			'4180			±180	
			'4200			±200	
V _(BO)	Breakover voltage	$dv/dt = \pm 250 \text{ V/ms}, R_{SOURCE} = 300 \Omega$	'4220			±220	V
* (BO)	Dioditovoi voitago	47/41 = 1200 7/110, 11 SOURCE = 000 12	4240			±240	·
			4250			±250	
			⁴ 265			±265	
			4203			±290	
			4230			±300	
			4300			±320	
		'4350					
					±350		
		'4360 '4365			±360		
			'4395			±395	
		'4070 '4080 '4095				±78	
						±88	
					±102		
			'4115 '4125			±122	
						±132	
			'4145			±151	
		'4165			±171		
		dv/dt ≤ ±1000 V/μs, Linear voltage ramp,	'4180			±186	
	Impulse breakover	Maximum ramp value = $\pm 500 \text{ V}$	'4200			±207	
$V_{(BO)}$	voltage	di/dt = ±20 A/μs, Linear current ramp,	'4220			±227	V
	voltage	Maximum ramp value = ±10 A	'4240			±247	
		Waximum ramp value = ±10 A	'4250			±257	
			'4265			±272	
			'4290			±298	
			'4300			±308	
			'4320			±328	
			'4350			±359	
			'4360			±370	
			'4395			±405	
I _(BO)	Breakover current	$dv/dt = \pm 250 \text{ V/ms}, R_{SOURCE} = 300 \Omega$		±0.15		±0.6	Α
V _T	On-state voltage	$I_T = \pm 5 \text{ A}, t_W = 100 \mu \text{s}$				±3	V
I _H	Holding current	$I_T = \pm 5$ A, di/dt = +/-30 mA/ms		±0.15		±0.35	Α
dv/dt	Critical rate of rise of off-state voltage	Linear voltage ramp, Maximum ramp value < 0.85V DRM		±5			kV/μs

Electrical Characteristics, TA = 25 °C (Unless Otherwise Noted)

	Parameter	Test Conditions	;	Min	Тур	Max	Unit
I _D	Off-state current	$V_D = \pm 50 \text{ V}$	T _A = 85 °C			±10	μΑ
		$f = 1 \text{ MHz}, V_d = 1 \text{ V rms}, V_D = 0,$	4070 thru '4115		83	100	
			'4125 thru '4220		62	74	
			'4240 thru '4400		50	60	
		$f = 1 \text{ MHz}, V_d = 1 \text{ V rms}, V_D = -1 \text{ V}$	'4070 thru '4115		78	94	
			'4125 thru '4220		56	67	
			'4240 thru '4395		45	54	
	O# -t-t:	$f = 1 \text{ MHz}, V_d = 1 \text{ V rms}, V_D = -2 \text{ V}$	'4070 thru '4115		72	87	~F
C _{off}	Off-state capacitance		'4125 thru '4220		52	62	pF
			'4240 thru '4395		42	50	
		$f = 1 \text{ MHz}, V_d = 1 \text{ V rms}, V_D = -50 \text{ V}$	'4070 thru '4115		36	44	
			'4125 thru '4220		26	31	
			'4240 thru '4400		19	22	
		$f = 1 \text{ MHz}, V_d = 1 \text{ V rms}, V_D = -100 \text{ V}$	'4125 thru '4220		21	25	
		(see Note 6)	'4240 thru '4395		15	18	

NOTE 6: To avoid possible voltage clipping, the '4125 is tested with $V_D = -98 \text{ V}$.

Thermal Characteristics

Parameter		Parameter Test Conditions		Тур	Max	Unit
$R_{ heta JA}$	Junction to free air thermal resistance	EIA/JESD51-3 PCB, $I_T = I_{TSM(1000)}$, $T_A = 25$ °C, (see Note 7)			115	°C/W
· ιθJΑ	oundin to not an institutionalities	265 mm x 210 mm populated line card, 4-layer PCB, I _T = I _{TSM(1000)} , T _A = 25 °C		52		0,77

NOTE 7: EIA/JESD51-2 environment and PCB has standard footprint dimensions connected with 5 A rated printed wiring track widths.

Parameter Measurement Information




Figure 1. Voltage-Current Characteristic for T and R Terminals All Measurements are Referenced to the R Terminal

Typical Characteristics

OFF-STATE CURRENT vs JUNCTION TEMPERATURE




Figure 2.

ON-STATE CURRENT vs

ON-STATE VOLTAGE TC4MACC 100 T_A = 25 °C 70 $t_{\rm W}$ = 100 μ s 50 40 30 I - On-State Current - A 20 15 10 7 '4125 **THRU** 5 '4200 4 3 2 '4240 '4070 **THRU THRU** 1.5 '4395 '4115

31

V_T - On-State Voltage - V Figure 4.

NORMALIZED BREAKOVER VOLTAGE





Figure 3.

NORMALIZED HOLDING CURRENT



Specifications are subject to change without notice.

0.7

Typical Characteristics


NORMALIZED CAPACITANCE

vs **OFF-STATE VOLTAGE** TC4MABC 1 0.9 $T_1 = 25$ °C 8.0 V_d = 1 Vrms Capacitance Normalzed to $V_D = 0$ 0.7 0.6 0.5 4070 THRU 4115 0.4 '4125 THRU '4200 0.3 '4240 THRU '4395 0.5 1 3 5 10 20 30 50 100 150 V_D - Off-state Voltage - V

Figure 6.

DIFFERENTIAL OFF-STATE CAPACITANCE

RATED REPETITIVE PEAK OFF-STATE VOLTAGE



TYPICAL CAPACITANCE ASYMMETRY

VS OFF-STATE VOLTAGE

TC4XBB


TC4XBB

V_d = 10 mVrms, 1 MHz

V_d = 1 Vrms, 1 MHz

Rating and Thermal Information

NON-REPETITIVE PEAK ON-STATE CURRENT




V_{DRM} DERATING FACTOR

VS MINIMUM AMBIENT TEMPERATURE 1.00 0.99 0.99 0.98 0.97 0.96 0.95 0.94 4240 THRU '4395 0.93 -40 -35 -30 -25 -20 -15 -10 -5 0 5 10 15 20 25 T_{AMIN} - Minimum Ambient Temperature - °C

Figure 10.


IMPULSE RATING



APPLICATIONS INFORMATION

Deployment

These devices are two terminal overvoltage protectors. They may be used either singly to limit the voltage between two conductors (Figure 12) or in multiples to limit the voltage at several points in a circuit (Figure 13).








Figure 13. Multi-Point Protection

In Figure 12, protector Th1 limits the maximum voltage between the two conductors to $\pm V(BO)$. This configuration is normally used to protect circuits without a ground reference, such as modems. In Figure 13, protectors Th2 and Th3 limit the maximum voltage between each conductor and ground to the $\pm V(BO)$ of the individual protector. Protector Th1 limits the maximum voltage between the two conductors to its $\pm V(BO)$ value. If the equipment being protected has all its vulnerable components connected between the conductors and ground, then protector Th1 is not required.

Impulse Testing

To verify the withstand capability and safety of the equipment, standards require that the equipment is tested with various impulse wave forms. The table below shows some common values.

Standard	Peak Voltage Setting V	Voltage Wave Shape μs	Peak Current Value A	Current Wave Shape μs	TISP4XXXM3 25 °C Rating A	Series Resistance Ω
GR-1089-CORE	2500	2/10	500	2/10	300	11
GI1-1009-0011L	1000	10/1000	100	10/1000	50	11
	1500	10/160	200	10/160	120	2x5.6
FCC Part 68	800	10/560	100	10/560	75	3
(March 1998)	1500	9/720 †	37.5	5/320 †	100	0
	1000	9/720 †	25	5/320 †	100	0
I3124	1500	0.5/700	37.5	0.2/310	100	0
ITU-T K.20/K.21	1500 4000	10/700	37.5 100	5/310	100	0

[†] FCC Part 68 terminology for the waveforms produced by the ITU-T recommendation K.21 10/700 impulse generator

If the impulse generator current exceeds the protector's current rating, then a series resistance can be used to reduce the current to the protector's rated value to prevent possible failure. The required value of series resistance for a given waveform is given by the following calculations. First, the minimum total circuit impedance is found by dividing the impulse generator's peak voltage by the protector's rated current. The impulse generator's fictive impedance (generator's peak voltage divided by peak short circuit current) is then subtracted from the minimum total circuit impedance to give the required value of series resistance.

For the FCC Part 68 10/560 waveform, the following values result. The minimum total circuit impedance is $800/75 = 10.7~\Omega$ and the generator's fictive impedance is $800/100 = 8~\Omega$. This gives a minimum series resistance value of $10.7 - 8 = 2.7~\Omega$. After allowing for tolerance, a $3~\Omega$ ±10% resistor would be suitable. The 10/160 waveform needs a standard resistor value of $5.6~\Omega$ per conductor. These would be R1a and R1b in Figure 15 and Figure 16. FCC Part 68 allows the equipment to be non-operational after the 10/160 (conductor to ground) and 10/560 (inter-conductor) impulses. The series resistor value may be reduced to zero to pass FCC Part 68 in a non-operational mode, e.g. Figure 14. For this type of design, the series fuse must open before the TISP4xxxM3 fails. For Figure 14, the maximum fuse i²t is $2.3~\text{A}^2\text{s}$. In some cases, the equipment will require verification over a temperature range. By using the rated waveform values from Figure 11, the appropriate series resistor value can be calculated for ambient temperatures in the range of -40 °C to 85 °C.

TISP4xxxM3AJ Overvoltage Protector Series

BOURNS

AC Power Testing

The protector can withstand currents applied for times not exceeding those shown in Figure 9. Currents that exceed these times must be terminated or reduced to avoid protector failure. Fuses, PTC (Positive Temperature Coefficient) thermistors and fusible resistors are overcurrent protection devices which can be used to reduce the current flow. Protective fuses may range from a few hundred milliamperes to one ampere. In some cases, it may be necessary to add some extra series resistance to prevent the fuse opening during impulse testing. The current versus time characteristic of the overcurrent protector must be below the line shown in Figure 9. In some cases, there may be a further time limit imposed by the test standard (e.g. UL 1459 wiring simulator failure).

Capacitance

The protector characteristic off-state capacitance values are given for d.c. bias voltage, VD, values of 0, -1 V, -2 V and -50 V. Where possible values are also given for -100 V. Values for other voltages may be calculated by multiplying the VD = 0 capacitance value by the factor given in Figure 6. Up to 10 MHz, the capacitance is essentially independent of frequency. Above 10 MHz, the effective capacitance is strongly dependent on connection inductance. In many applications, such as Figure 15 and Figure 17, the typical conductor bias voltages will be about -2 V and -50 V. Figure 7 shows the differential (line unbalance) capacitance caused by biasing one protector at -2 V and the other at -50 V.

Figure 8 shows the typical capacitance asymmetry; the difference between the capacitance measured with a positive value of VD and the capacitance value when the polarity of VD is reversed. Capacitance asymmetry is an important parameter in ADSL systems where the protector often has no d.c. bias and the signal level is in the region of ±10 V.

Normal System Voltage Levels

The protector should not clip or limit the voltages that occur in normal system operation. For unusual conditions, such as ringing without the line connected, some degree of clipping is permissible. Under this condition, about 10 V of clipping is normally possible without activating the ring trip circuit.

Figure 10 allows the calculation of the protector VDRM value at temperatures below 25 °C. The calculated value should not be less than the maximum normal system voltages. The TISP4265M3AJ, with a VDRM of 200 V, can be used for the protection of ring generators producing 100 V rms of ring on a battery voltage of -58 V (Th2 and Th3 in Figure 17). The peak ring voltage will be 58 + 1.414*100 = 199.4 V. However, this is the open circuit voltage and the connection of the line and its equipment will reduce the peak voltage. In the extreme case of an unconnected line, clipping the peak voltage to 190 V should not activate the ring trip. This level of clipping would occur at the temperature when the VDRM has reduced to 190/200 = 0.95 of its 25 °C value. Figure 10 shows that this condition will occur at an ambient temperature of -28 °C. In this example, the TISP4265M3AJ will allow normal equipment operation provided that the minimum expected ambient temperature does not fall below -28 °C.

JESD51 Thermal Measurement Method

To standardize thermal measurements, the EIA (Electronic Industries Alliance) has created the JESD51 standard. Part 2 of the standard (JESD51-2, 1995) describes the test environment. This is a 0.0283 m³ (1 ft³) cube which contains the test PCB (Printed Circuit Board) horizontally mounted at the center. Part 3 of the standard (JESD51-3, 1996) defines two test PCBs for surface mount components; one for packages smaller than 27 mm on a side and the other for packages up to 48 mm. The SMBJ measurements used the smaller 76.2 mm x 114.3 mm (3.0 " x 4.5") PCB. The JESD51-3 PCBs are designed to have low effective thermal conductivity (high thermal resistance) and represent a worst case condition. The PCBs used in the majority of applications will achieve lower values of thermal resistance, and can dissipate higher power levels than indicated by the JESD51 values.

Typical Circuits




Figure 14. Modem Inter-Wire Protection




Figure 15. Protection Module




Figure 16. ISDN Protection





Figure 17. Line Card Ring/Test Protection

MECHANICAL DATA

Recommended Printed Wiring Footprint



MDXX BIC

Device Symbolization Code

Devices will be coded as below. As the device parameters are symmetrical, terminal 1 is not identified.

Device	Symbolization Code
TISP4070M3AJ	4070M
TISP4080M3AJ	4080M
TISP4095M3AJ	4095M
TISP4115M3AJ	4115M
TISP4125M3AJ	4125M
TISP4145M3AJ	4145M
TISP4165M3AJ	4165M
TISP4180M3AJ	4180M
TISP4200M3AJ	4200M
TISP4220M3AJ	4220M
TISP4240M3AJ	4240M
TISP4250M3AJ	4250M
TISP4265M3AJ	4265M
TISP4290M3AJ	4290M
TISP4300M3AJ	4300M
TISP4350M3AJ	4350M
TISP4360M3AJ	4360M
TISP4395M3AJ	4395M

Carrier Information

For production quantities, the carrier will be embossed tape reel pack. Evaluation quantities may be shipped in bulk pack or embossed tape.

Carrier	Standard Quantity
Embossed Tape Reel Pack	5,000

[&]quot;TISP" is a trademark of Bourns, Ltd., a Bourns Company, and is Registered in the U.S. Patent and Trademark Office. "Bourns" is a registered trademark of Bourns, Inc. in the U.S. and other countries.

NOVEMBER 1997 - REVISED MARCH 2023

Specifications are subject to change without notice.

Users should verify actual device performance in their specific applications.

Legal Disclaimer Notice



This legal disclaimer applies to purchasers and users of Bourns® products manufactured by or on behalf of Bourns, Inc. and its affiliates (collectively, "Bourns").

Unless otherwise expressly indicated in writing, Bourns® products and data sheets relating thereto are subject to change without notice. Users should check for and obtain the latest relevant information and verify that such information is current and complete before placing orders for Bourns® products.

The characteristics and parameters of a Bourns® product set forth in its data sheet are based on laboratory conditions, and statements regarding the suitability of products for certain types of applications are based on Bourns' knowledge of typical requirements in generic applications. The characteristics and parameters of a Bourns® product in a user application may vary from the data sheet characteristics and parameters due to (i) the combination of the Bourns® product with other components in the user's application, or (ii) the environment of the user application itself. The characteristics and parameters of a Bourns® product also can and do vary in different applications and actual performance may vary over time. Users should always verify the actual performance of the Bourns® product in their specific devices and applications, and make their own independent judgments regarding the amount of additional test margin to design into their device or application to compensate for differences between laboratory and real world conditions.

Unless Bourns has explicitly designated an individual Bourns® product as meeting the requirements of a particular industry standard (e.g., ISO/TS 16949) or a particular qualification (e.g., UL listed or recognized), Bourns is not responsible for any failure of an individual Bourns® product to meet the requirements of such industry standard or particular qualification. Users of Bourns® products are responsible for ensuring compliance with safety-related requirements and standards applicable to their devices or applications.

Bourns® products are not recommended, authorized or intended for use in nuclear, lifesaving, life-critical or life-sustaining applications, nor in any other applications where failure or malfunction may result in personal injury, death, or severe property or environmental damage. Unless expressly and specifically approved in writing by two authorized Bourns representatives on a case-by-case basis, use of any Bourns® products in such unauthorized applications might not be safe and thus is at the user's sole risk. Life-critical applications include devices identified by the U.S. Food and Drug Administration as Class III devices and generally equivalent classifications outside of the United States.

Bourns expressly identifies those Bourns® standard products that are suitable for use in automotive applications on such products' data sheets in the section entitled "Applications." Unless expressly and specifically approved in writing by two authorized Bourns representatives on a case-by-case basis, use of any other Bourns® standard products in an automotive application might not be safe and thus is not recommended, authorized or intended and is at the user's sole risk. If Bourns expressly identifies a sub-category of automotive application in the data sheet for its standard products (such as infotainment or lighting), such identification means that Bourns has reviewed its standard product and has determined that if such Bourns® standard product is considered for potential use in automotive applications, it should only be used in such sub-category of automotive applications. Any reference to Bourns® standard product in the data sheet as compliant with the AEC-Q standard or "automotive grade" does not by itself mean that Bourns has approved such product for use in an automotive application.

Bourns® standard products are not tested to comply with United States Federal Aviation Administration standards generally or any other generally equivalent governmental organization standard applicable to products designed or manufactured for use in aircraft or space applications. Bourns expressly identifies Bourns® standard products that are suitable for use in aircraft or space applications on such products' data sheets in the section entitled "Applications." Unless expressly and specifically approved in writing by two authorized Bourns representatives on a case-by-case basis, use of any other Bourns® standard product in an aircraft or space application might not be safe and thus is not recommended, authorized or intended and is at the user's sole risk.

The use and level of testing applicable to Bourns® custom products shall be negotiated on a case-by-case basis by Bourns and the user for which such Bourns® custom products are specially designed. Absent a written agreement between Bourns and the user regarding the use and level of such testing, the above provisions applicable to Bourns® standard products shall also apply to such Bourns® custom products.

Users shall not sell, transfer, export or re-export any Bourns® products or technology for use in activities which involve the design, development, production, use or stockpiling of nuclear, chemical or biological weapons or missiles, nor shall they use Bourns® products or technology in any facility which engages in activities relating to such devices. The foregoing restrictions apply to all uses and applications that violate national or international prohibitions, including embargos or international regulations. Further, Bourns® products and Bourns technology and technical data may not under any circumstance be exported or re-exported to countries subject to international sanctions or embargoes. Bourns® products may not, without prior authorization from Bourns and/or the U.S. Government, be resold, transferred, or re-exported to any party not eligible to receive U.S. commodities, software, and technical data.

To the maximum extent permitted by applicable law, Bourns disclaims (i) any and all liability for special, punitive, consequential, incidental or indirect damages or lost revenues or lost profits, and (ii) any and all implied warranties, including implied warranties of fitness for particular purpose, non-infringement and merchantability.

For your convenience, copies of this Legal Disclaimer Notice with German, Spanish, Japanese, Traditional Chinese and Simplified Chinese bilingual versions are available at:

Web Page: http://www.bourns.com/legal/disclaimers-terms-and-policies

PDF: http://www.bourns.com/docs/Legal/disclaimer.pdf