


# MATERIAL DECLARATION SHEET



Material Number	1280 series			
Product Line	SPD			
Compliance Date	Mar 2024			
RoHS Compliant	Yes	MSL	1	

NO	Construction Element (subpart)	Homogeneous Materials	Material weight [g]	Homogeneous Material	CASRN	Materials Mass %	Material Mass % of total unit wt.	Subpart mass of total wt • (%)
				Substances	if applicable			
1	Varistor	Ceramic	34.3000	Zinc oxide	1314-13-2	99.000%	24.354%	24.600%
				Bismuth oxide	1304-76-3	0.200%	0.049%	
				Cobalt oxide	1308-04-9	0.200%	0.049%	
				Antimony oxide	1332-81-6	0.200%	0.049%	
				Manganese oxide	1317-34-6	0.100%	0.025%	
				Titanium oxide	13463-67-7	0.050%	0.012%	
				Boron oxide	1303-86-2	0.100%	0.025%	
				Chromium Oxide	1118-57-3	0.100%	0.025%	
				Silver nitrate	7761-88-8	0.050%	0.012%	
		Termination	1.1100	Silver	7440-22-4	100.000%	0.796%	0.796%
		Encapsulating material	2.2000	Glycidyl terminated bisphenol A epoxy chloropropane copolymer	25036-25-3	45.700%	0.721%	1.578%
				Silica	60676-86-0	31.200%	0.492%	
				Titanium dioxide	13463-67-7	2.800%	0.044%	
				Trimellitic anhydride	552-30-7	3.300%	0.052%	
Basic copper carbonate	12069-69-1			3.500%	0.055%			
Zirconium silicate	10101-52-7			7.000%	0.110%			
Misc not to declare		---		6.500%	0.103%			

# MATERIAL DECLARATION SHEET



		Terminal	7.1928	Copper	7440-50-8	99.970%	5.157%	5.159%
				Traces not to declare	---	0.030%	0.002%	
		Nickel plate	0.0036	Nickel	7440-22-40	100.000%	0.003%	0.003%
		Silver plate	0.0036	Silver	7440-02-0	100.000%	0.003%	0.003%
2	Plastic shell	PBT	47.8000	PBT resin	26062-94-2	55.000%	18.855%	34.282%
				Halogen flame retardant	68928-70-1	13.000%	4.457%	
				Antimony oxide	1309-64-4	5.000%	1.714%	
				Glass fiber	65997-17-3	20.000%	6.856%	
				Misc not to declare	---	7.000%	2.400%	
3	Spring	Spring	0.3000	Iron	7439-89-6	98.000%	0.211%	0.215%
				Manganese	7439-96-5	0.650%	0.001%	
				Carbon	7440-44-0	0.650%	0.001%	
				Silicon	7440-21-3	0.200%	0.000%	
				Misc not to declare	---	0.500%	0.001%	
4	Switch	PPA	1.4000	Modified hexanediamide terephthalate	25776-72-1	65.000%	0.653%	1.004%
				Glass fiber	65997-17-3	32.000%	0.321%	
				Processing aids	1333-86-4	3.000%	0.030%	
		SUS304	0.1000	Iron	7439-89-6	70.000%	0.050%	0.072%
				Nickel	7440-02-0	10.000%	0.007%	
				Chromium	7440-47-3	18.000%	0.013%	
				Manganese	7439-96-5	2.000%	0.001%	
		SUS301	0.1000	Iron	7439-89-6	72.000%	0.052%	0.072%
				Nickel	7440-02-0	8.000%	0.006%	
				Chromium	7440-47-3	18.000%	0.013%	
				Manganese	7439-96-5	2.000%	0.001%	
		Copper part	0.0200	Copper	7440-50-8	61.500%	0.009%	0.014%
				Zinc	7440-66-6	38.465%	0.006%	

# MATERIAL DECLARATION SHEET



				Phosphorus	7723-14-0	0.006%	0.000%	
				Lead	7439-92-1	0.005%	0.000%	
				Iron	7439-89-6	0.020%	0.000%	
				Misc not to declare	---	0.005%	0.000%	
5	Copper Electrode	Copper part	21.0000	Copper	7440-50-8	91.550%	13.789%	15.061%
				Tin	7440-31-5	8.000%	1.205%	
				Zinc	7440-66-6	0.300%	0.045%	
				Phosphorus	7723-14-0	0.150%	0.023%	
6	Low-temperature alloys	Alloys Solder	1.0000	Tin	7440-31-5	42.000%	0.301%	0.717%
				Bismuth	7440-69-9	58.000%	0.416%	
7	Screw	SUS304 Part	13.6000	Carbon	7440-44-0	0.070%	0.007%	9.754%
				Manganese	7439-96-5	1.200%	0.117%	
				Silicon	7440-21-3	0.700%	0.068%	
				Phosphorus	7723-14-0	0.020%	0.002%	
				Sulfur	7704-34-9	0.010%	0.001%	
				Nickel	7440-02-0	11.000%	1.073%	
				Chromium	7440-47-3	18.000%	1.756%	
				Iron	7439-89-6	69.000%	6.730%	
8	GDT	Ceramic tube	1.5503	Alumina	1344-28-1	100.000%	1.112%	1.112%
		Iron Nickel Alloy	1.0388	Iron	7439-89-6	58.000%	0.432%	0.745%
				Nickel	7440-02-0	42.000%	0.313%	
		Tungsten	5.5158	Tungsten	7440-33-7	60.000%	2.374%	3.956%
				Copper	7440-50-8	40.000%	1.582%	
		AgCu28	0.2083	Silver	7440-22-4	72.000%	0.108%	0.149%
				Copper	7440-50-8	28.000%	0.042%	
		Copper	0.1973	Copper	7440-50-8	100.000%	0.142%	0.142%
Tin plate	0.7894	Tin	7440-31-5	100.000%	0.566%	0.566%		
		<b>Total</b>	<b>139.4300</b>					

**This Document was updated on: Mar 2024**

**Important remarks:**

1. It is the responsibility of the user to verify they are accessing the latest version.