


MATERIAL DECLARATION SHEET



Material Number	3547H-1xE-xxx			
Product Line	Sensors & Controls			
Compliance Date	2/12/2025			
RoHs Compliant	Yes	MSL	N/A	

No.	Construction Element(subpart)	Homogeneous Material	Material weight [g]	Homogeneous Material	CASRN	Materials Mass %	Material Mass % of total unit wt.	Subpart mass of total wt. (%)
				Substances	if applicable			
1	Ball Bearing	Stainless Steel 400C Martensitic	0.3000	Chromium	7440-47-3	13	0.126	0.97
				Carbon	7440-44-0	0.15	0.001	
				Silicon	7440-21-3	1	0.010	
				Manganese	7439-96-5	1	0.010	
				Iron	7439-89-6	84.85	0.823	
2	Servo Lid	Aluminum 2011	0.00406	Silicon	7440-21-3	0.4	0.0001	0.01
				Iron	7439-89-6	0.7	0.0001	
				Copper	7440-50-8	5	0.00066	
				Zinc	7440-66-6	0.3	0.00004	
				Misc., not to declare	Trade Secret	0.15	0.00002	
				Aluminum	7429-90-5	92.925	0.01	
				Bismuth	7440-69-9	0.325	0.00004	
Lead	7439-92-1	0.2	0.00003					
3	Terminal Wiper	Brass C260	0.3000	Copper	7440-50-8	70	0.679	0.97
				Zinc	7440-66-6	30	0.29	
		Under Plating	0.0120	Nickel	7440-02-0	100	0.039	
		Finish Plating	0.0274	Gold	7440-57-5	100	0.089	
4	Cover	GS-51 Nylatron	1.642004	Nylon 6.6 (polyhexamethylene adipamide)	32131-17-2	66	3.50	5.31

MATERIAL DECLARATION SHEET



				Glass Fiber	65997-17-3	32	1.70	
				Molybdenum Disulfide	1317-33-5	2	0.11	
5	Housing	ShinKong compound (Black)	7.893	PBT	26062-94-2	53.7	13.70	25.52
				Glass Fiber	65997-17-3	30	7.6554	
				Brominated Epoxy Resin	68928-70-1	10.5	2.6794	
				Antimony Trioxide	1309-64-4	3	0.7655	
				Pigment Blue 15	147-14-8	0.8	0.2041	
				Further Additives, not to declare	N/A	2	0.5104	
6	Varnish	Varnish	0.052	Phenolic Resin	9003-35-4	100	0.1681	0.17
7	Mandrel Wire	Annealed Copper Wire	1.6848122	Copper	7440-50-8	100	5.45	5.45
		Coating	0.0000312	Polyamide	63428-83-1	100	0.00010	0.0001
8	Resist Wire	Nickel/Chromium Alloy	0.13414	Nickel	7440-02-0	74	0.32	0.43
				Copper	7440-50-8	1	0.004	
				Chromium	7440-47-3	21	0.09	
				Aluminum	7429-90-5	1	0.004	
				Silicon	7440-21-3	1	0.004	
				Cobalt	7440-48-4	1	0.004	
9	Collector Bar	Nickel/Silver C762	0.063	Copper	7440-50-8	55	0.112	0.20
				Nickel	7440-02-0	18	0.04	
				Zinc	7440-66-6	27	0.0550	
		Plating	0.002	Gold	7440-57-5	100	0.006	0.006

MATERIAL DECLARATION SHEET



10	Lube	NYE N799	0.1	Decanoic acid, mixed esters with heptanoic acid, octanoic acid, trimethylolpropane	68130-53-0	54.4	0.18	0.32
				Lithium 12-hydroxystearate	7620-77-1	5.7	0.018	
				Isohexadecyl-isooctadecanoate	52006-45-8	33.7	0.11	
				Polyisobutylene	9003-27-4	6.2	0.020	
11	Epoxy	BLUE EPOXY E940	0.00563	Epoxy Resin	25068-38-6	64	0.012	0.018
				Antimony Trioxide	1309-64-4	11	0.0020	
				Aluminum Oxide	1344-28-1	10	0.002	
				Kaolin Clay	1332-58-7	6	0.0011	
				Magnesium Aluminum Silicate	1327-43-1	9	0.0016	
12	Rotor Molded	GS-51 Nylatron	2.74877	Nylon 6.6 (polyhexamethylene adipamide)	32131-17-2	66	5.87	8.89
				Glass Fiber	65997-17-3	32	2.84	
				Molybdenum Disulfide	1317-33-5	2	0.178	
13	Slider Molded	GS-51 Nylatron	0.7937866	Nylon 6.6 (polyhexamethylene adipamide)	32131-17-2	66	1.694	2.57
				Glass Fiber	65997-17-3	32	0.821	
				Molybdenum Disulfide	1317-33-5	2	0.051	
14	Lid Molded	ShinKong compound (Black)	2.2112628	PBT	26062-94-2	53.7	3.839	7.15
				Glass Fiber	65997-17-3	30	2.145	
				Brominated Epoxy Resin	68928-70-	10.5	0.751	

MATERIAL DECLARATION SHEET



					1			
				Antimony Trioxide	1309-64-4	3	0.214	
				Pigment Blue 15	147-14-8	0.8	0.057	
				Further Additives, not to declare	N/A	2	0.143	
15	Contact Spring	Pfinodal 7 C72900	0.01	Copper	7440-50-8	72.875	0.02	0.03
				Lead	7439-92-1	0.025	0.00001	
				Iron	7439-89-6	0.3	0.0001	
				Nickel	7440-02-0	21	0.0068	
				Cobalt	7440-48-4	0.25	0.0001	
				Tin	7440-31-5	5.1	0.001649	
				Manganese	7439-96-5	0.3	0.000097	
	Misc	Not to declare	0.15	0.000048				
	Paliney #6	0.003	Palladium	7440-05-3	39.8	0.003860	0.01	
			Silver	7440-22-4	33.9	0.003288		
			Copper	7440-50-8	24.2	0.002347		
			Platinum	7440-06-4	0.5	0.000048		
			Nickel	7440-02-0	1.59	0.000154		
Zinc			7440-66-6	0.01	0.000001			
16	Shaft	Stainless Steel 303	6.89	Carbon	7440-44-0	0.15	0.03	22.28
				Manganese	7439-96-5	2	0.45	
				Phosphorus	7723-14-0	0.2	0.04	
				Sulfur	7704-34-9	0.15	0.03	
				Silicon	7440-21-3	0.9	0.20	
				Chromium	7440-47-3	18	4.01	
				Nickel	7440-02-0	9	2.00	
				Iron	7439-89-6	69	15.37	
Molybdenum	7439-98-7	0.6	0.13					
17	Retaining Ring	Stainless Steel 420	0.009	Carbon	7440-44-0	0.15	0.00004	0.03

MATERIAL DECLARATION SHEET



				Manganese	7439-96-5	1.00	0.0003	
				Silicon	7440-21-3	1.00	0.0003	
				Phosphorous	7723-14-0	0.04	0.00001	
				Sulfur	7704-34-9	0.30	0.00009	
				Chromium	7440-47-3	14.00	0.004	
				Iron	7439-89-6	83.51	0.024	
18	Bushing	Brass C360	3.71	Copper	7440-50-8	61.50	7.377	11.99
				Zinc	7440-66-6	35.40	4.246	
				Lead	7439-92-2	3.10	0.372	
19	T.R. Terminal x2	Nickel/Silver C752	0.164	Copper	7440-50-8	65.00	0.345	0.53
				Nickel	7440-02-0	18.00	0.095	
				Zinc	7440-66-6	17.00	0.090	
		Solder Inlay	0.0001	Silver	7440-22-4	56.00	0.0002	0.0003
				Copper	7440-50-8	22.00	0.0001	
				Zinc	7440-66-6	17.00	0.00005	
				Tin	7440-31-5	5.00	0.00002	
Plating	0.00074	Gold	7440-57-5	100.00	0.002	0.002		
20	T.R. Pin Strip	Nickel Silver CDA752	0.249	Nickel	7440-02-0	18.00	0.145	0.805
				Copper	7440-50-8	65.00	0.523	
				Zinc	7440-66-6	17.00	0.137	
21	Terminal Cover	GS-51 Nylatron	1.367581	Nylon 6.6 (polyhexamethylene adipamide)	32131-17- 2	66.00	2.918	4.42
				Glass fiber	65997-17- 3	32.00	1.415	
				Molybdenum disulfide	1317-33-5	2.00	0.088	
22	Lid Resin	Valox 420	0.003	PBT	30965-26- 5	55.00	0.0053	0.01
				Glass Fiber	65997-17- 3	30.00	0.002910	
				Antimony Trioxide	1309-64-4	4.00	0.000388	

MATERIAL DECLARATION SHEET



				Brominated FR (TBBPA polycarbonate polymer)	trade secret	11.00	0.001067	
23	Insert	Aluminum 2011	0.085	Silicon	7440-21-3	0.40	0.001099	0.27
				Iron	7439-89-6	0.70	0.001924	
				Copper	7440-50-8	5.00	0.013740	
				Zinc	7440-66-6	0.30	0.000824	
				Misc., not to declare	Trade Secret	0.15	0.000412	
				Aluminum	7429-90-5	92.93	0.255363	
				Bismuth	7440-69-9	0.33	0.000893	
				Lead	7439-92-1	0.20	0.000550	
24	Ink	138:Hyb. Beta/Gamma	0.17	3-chloroprop-1-ene, formaldehyde, phenol	28470-78-2	38.00	0.208852	0.55
				Carbon Black	1333-86-4	20.70	0.113769	
				Diallyl Isophthalate	1087-21-4	35.80	0.196760	
				Graphite	7782-42-5	5.50	0.030229	
25	Tab	Silver Alloy A56T	0.013312288	Silver	7440-22-4	56.00	0.024102	0.04
				Copper	7440-50-8	22.00	0.009468	
				Zinc	7440-66-6	17.00	0.007317	
				Tin	7440-31-5	5.00	0.002152	
		Strip	0.1924	Nickel	7440-02-0	100.00	0.622029	0.62
26	Lube	Versilube G321	0.09	Siloxanes and Silicones, di-Me, di-Ph	68083-14-7	68.90	0.200478	0.29
				Lithium stearate	4485-12-5	25.40	0.073906	
				Silane, dichlorodimethyl-reaction products with silica	68611-44-9	4.80	0.013967	
				Diphenylamine	122-39-4	0.90	0.002619	
		Total weight	30.9310					

MATERIAL DECLARATION SHEET

BOURNS®

This Document was updated on: 2/12/2025

Important remarks:

1. It is the responsibility of the user to verify they are accessing the latest version.