


MATERIAL DECLARATION SHEET



Material Number	UV			
Product Line	Fixed Resistor			
Compliance Date	10/10/2024			
RoHS Compliant		MSL	1	

Reference P/N: UV10-5R3J1 (Under 40 Ohm)

No.	Construction Element (Subpart)	Homogeneous Material	Material Weight (g)	Homogeneous Material Substance	CASRN	Material Mass %	Material Mass % of total unit wt.	Subpart mass of total wt. (%)
1	Ceramic Core	Ceramic	2.0400	Silicon Dioxide (SiO ₂)	7631-86-9	14.5000%	1.4485%	9.9895%
				Magnesium (Mg)	7439-95-4	1.1300%	0.1129%	
				Aluminum (Al)	7429-90-5	83.3200%	8.3232%	
				Barium (Ba)	7440-39-3	1.0500%	0.1049%	
2	Ceramic Cap	Iron	0.1500	Iron (Fe)	7439-89-6	99.9000%	0.7338%	0.7345%
				Tin (Sn)	7440-31-5	0.1000%	0.0007%	
3	Terminal	Copper C10100	0.233994	Copper (Cu)	7440-50-8	99.9954%	1.1458%	1.1458%
		Tin Plating		0.006006	Trace not to declare		0.0046%	
4	Resistive Element	Cuprothal	0.2946	Tin (Sn)	7440-31-5	100.0000%	0.0294%	1.4426%
				Nickel (Ni)	7440-02-0	44.0000%	0.6347%	
				Iron (Fe)	7439-89-6	0.5000%	0.0072%	
				Manganese (Mn)	7439-96-5	1.0000%	0.0144%	
5	Silicon coat	Silicon	0.0920	Copper (Cu)	7440-50-8	54.5000%	0.7862%	0.4505%
				Silica, amorphous	112926-00-8	31.2000%	0.1406%	
				Silica, crystalline - Tripoli	1317-95-9	25.0000%	0.1126%	
				Kaolin	1332-58-7	12.9000%	0.0581%	
				Carbon black	1333-86-4	0.6000%	0.0027%	
6	Cement	Cement	8.5049	Mica	12001-26-2	12.9000%	0.0581%	41.6468%
				Trimethoxy(methyl)silane	1185-55-3	17.4000%	0.0784%	
				Phosphoric Acid, Magnesium Salt	7757-86-0	14.0000%	5.8306%	
				zircon (zr(sio ₄))	14940-68-2	73.0000%	30.4022%	
7	Ceramic Boat	Boat	9.1000	Magnesium Oxide	1309-48-4	12.0000%	4.9976%	44.5609%
				Boric Acid	10043-35-3	1.0000%	0.4165%	
		Total Weight	20.4215	Kaolin Powder	1332-58-7	100.0000%	44.5609%	44.5609%

MATERIAL DECLARATION SHEET



Reference P/N: UV10-100RJ1 (Over 40 Ohm)

No.	Construction Element (Subpart)	Homogeneous Material	Material Weight (g)	Homogeneous Material Substance	CASRN	Material Mass %	Material Mass % of total unit wt.	Subpart mass of total wt. (%)
1	Ceramic Core	Ceramic	2.0400	Silicon Dioxide (SiO ₂)	7631-86-9	14.5000%	1.4643%	10.0987%
				Magnesium (Mg)	7439-95-4	1.1300%	0.1141%	
				Aluminum (Al)	7429-90-5	83.3200%	8.4142%	
				Barium (Ba)	7440-39-3	1.0500%	0.1060%	
2	Ceramic Cap	Iron	0.1500	Iron (Fe)	7439-89-6	99.9000%	0.7418%	0.7426%
				Tin (Sn)	7440-31-5	0.1000%	0.0007%	
3	Terminal	Copper C10100	0.233994	Copper (Cu)	7440-50-8	99.9954%	1.1583%	1.1584%
		Tin Plating	0.006006	Trace not to declare		0.0046%	0.0001%	
						Tin (Sn)	7440-31-5	100.0000%
4	Resistive Element	EVNOM Alloy	0.0737	Nickel (Ni)	7440-02-0	74.4000%	0.2714%	0.3648%
				Chromium (Cr)	7440-47-3	20.0000%	0.0730%	
				Aluminum (Al)	7429-90-5	3.5000%	0.0128%	
				Silicon (Si)	7440-21-3	1.0000%	0.0036%	
				Iron (Fe)	7439-89-6	0.5000%	0.0018%	
				Manganese (Mn)	7439-96-5	0.5000%	0.0018%	
				Copper (Cu)	7440-50-8	0.1000%	0.0004%	
5	Silicon coat	Silicon	0.0920	Silica, amorphous	112926-00-8	31.2000%	0.1421%	0.4554%
				Silica, crystalline - Tripoli	1317-95-9	25.0000%	0.1139%	
				Kaolin	1332-58-7	12.9000%	0.0588%	
				Carbon black	1333-86-4	0.6000%	0.0027%	
				Mica	12001-26-2	12.9000%	0.0588%	
				Trimethoxy(methyl)silane	1185-55-3	17.4000%	0.0792%	
6	Cement	Cement	8.5049	Phosphoric Acid, Magnesium Salt zircon (zr(sio ₄))	7757-86-0	14.0000%	5.8943%	42.1022%
				Magnesium Oxide	14940-68-2	73.0000%	30.7346%	
				Boric Acid	1309-48-4	12.0000%	5.0523%	
					10043-35-3	1.0000%	0.4210%	
7	Ceramic Boat	Boat	9.1000	Kaolin Powder	1332-58-7	100.0000%	45.0482%	45.0482%
		Total Weight	20.2006					

MATERIAL DECLARATION SHEET

BOURNS®

This Document was updated on: 10/16/2024

Important remarks:

1. It is the responsibility of the user to verify they are accessing the latest version.
2. Resistive material weight will be different based on the resistance value.
3. The weight of the core and coating material will differ based on the size.