



## Bourns Releases New AEC-Q200 Compliant, Automotive Grade Shielded Power Inductors

### Model SRR0735HA and SRR0745HA Series

Riverside, California – January 11, 2024 – Bourns Magnetics Product Line is introducing the new Automotive Grade Model [SRR0735HA](#) and [SRR0745HA](#) Series High Temperature Shielded Power Inductors. These power inductors are designed with a ferrite core and ferrite shield for low magnetic field radiation, making them ideal for applications where low noise operating environments are essential.

The Model SRR0735HA and SRR0745HA Series are AEC-Q200 compliant and automotive grade, featuring a broad operating temperature range of -55 °C to +150 °C. These inductors are well suited for automotive systems, DC/DC converters, and power supplies in automotive, consumer, industrial, and telecom applications in which higher inductor reliability may be required.

#### Characteristics:

Series	Size (mm)	Inductance (μH)	Heating Current $I_{rms}$ (A)	Saturation Current $I_{sat}$ (A)	Operating Temperature (°C)
SRR0735HA	7.3 x 7.3 x 3.5	10 - 1000	0.17 - 2.1	0.18 – 1.85	-55 to +150
SRR0745HA	7.3 x 7.3 x 4.5	10 - 1000	0.2 - 2.1	0.24 – 2.5	-55 to +150

Please visit the Bourns website at [www.bourns.com](http://www.bourns.com) for additional product details and contact [Bourns Customer Service/Inside Sales](#) if you have any questions.

#### Features

- Shielded construction – low radiation
- Wide operating temperature range
- RoHS compliant\* and halogen free\*\*
- AEC-Q200 compliant
- **AUTOMOTIVE GRADE**

#### Applications

- Automotive systems
- DC-DC converters
- Power supplies in consumer, industrial, and telecom electronics

\* RoHS Directive 2015/863, Mar 31, 2015 and Annex.

\*\* Bourns considers a product to be "halogen free" if (a) the Bromine (Br) content is 900 ppm or less; (b) the Chlorine (Cl) content is 900 ppm or less; and (c) the total Bromine (Br) and Chlorine (Cl) content is 1500 ppm or less.

IC23126B