


New Product Release

SINGL FUSE™ SMD FUSES



Bourns SinglFuse Product Line Announces New SMD Slow Blow Wire Core Fuses

Model SF-1206SxxxW & SF-1210SxxxW Series

Riverside, California - March 29, 2018 - Bourns is pleased to announce the introduction of two new lines of slow blow wire core SinglFuse™ SMD Fuses in 1206 and 1210 footprints to complement its already successful line of SinglFuse™ SMD Fuse products.

Series	Size	Fuse Type	Rated Current	Rated Voltage	UL Listed	RoHS Compliant*	Halogen Free**
SF-1206SxxxW	1206 (3216)	Slow Blow	1.5 A to 4.0 A	65 Vdc	Yes	Yes	Yes
			5.0 A to 15 A	32 Vdc			
SF-1210SxxxW	1210 (3225)	Slow Blow	1.0 A to 3.0 A	125 Vac	Yes	Yes	Yes

Bourns continues to broaden its portfolio of [SinglFuse™ SMD Fuses](#) to address the growing need for effective circuit protection in a variety of applications including PCs and monitors, server farms, portable memory, cell phones and tablets, digital cameras, gaming systems, set-top boxes, drones and robotics, white goods, battery chargers, and industrial controllers. The Bourns® SinglFuse™ SMD Fuse products are RoHS compliant* and halogen free**.

Please visit the Bourns website at www.bourns.com for additional product details. If you have any questions or need additional information, please feel free to contact [Bourns Customer Service/Inside Sales](#).

Features

- Single blow fuse for overcurrent protection
- 1206 (3216) and 1210 (3225) footprint
- Slow blow fuse
- UL 248-14 listed
- Surface mount packaging for automated assembly
- Wire core SMD design
- RoHS compliant* and halogen free**

* RoHS Directive 2015/863, Mar 31, 2015 and Annex.

** Bourns considers a product to be "halogen free" if (a) the Bromine (Br) content is 900 ppm or less; (b) the Chlorine (Cl) content is 900 ppm or less; and (c) the total Bromine (Br) and Chlorine (Cl) content is 1500 ppm or less.