



Features

- Weather resistant enclosure with hinged cover
- Two pair, 24 gauge buried service wire pigtailed available
- May be mounted on trailer tongue with steel beam clamp or structure with outside mounting brackets
- Four (4) terminal posts plus a ground terminal with associated hardware
- Rubber grommet entry port

7060 Series - Terminal Device

Bourns 7060 Series Mobile Home Terminal Housing is designed to provide solutions for telephone service to semi-permanent or mobile subscriber dwellings. The various configurations available will accommodate almost every temporary hook-up condition.

The 7060 is a versatile, weather resistant enclosure, manufactured of high-impact resistant, ultraviolet-desensitized, flame retardant plastic.

How to Order

- 7060-01 Unit supplied with beam clamp and 10 ' pigtail of two-pair 24 gauge buried service wire
- 7060-02 Unit supplied with beam clamp and 35 ' pigtail of two-pair 24 gauge buried service wire
- 7060-03 Unit supplied with 10 ' pigtail of two-pair 24 gauge buried service wire – no beam clamp
- 7060-04 Unit supplied with 35 ' pigtail of two-pair 24 gauge buried service wire – no beam clamp
- 7060-05 Unit supplied as four post terminal box; no pigtail wire and no beam clamp

For other options, please contact factory.

Product Dimensions

High	Wide	Deep
$\frac{144.8}{(5.7)}$	$\frac{86.4}{(3.4)}$	$\frac{53.3}{(2.1)}$

DIMENSIONS: $\frac{\text{MM}}{\text{(INCHES)}}$

NOTE: IN ACCORDANCE WITH ONGOING PRODUCT LIFECYCLE MANAGEMENT PROCEDURES, BOURNS HAS ENTERED INTO AN AGREEMENT TO TRANSFER ITS NID PRODUCT LINE TO TELECOMMUNICATION DEVICES INC. (TDI) EFFECTIVE 1/1/2019.

REV. D

Specifications are subject to change without notice.
Customers should verify actual device performance in their specific applications