
## BD245, BD245A, BD245B, BD245C NPN SILICON POWER TRANSISTORS

# BOURNS®

- Designed for Complementary Use with the BD246 Series
- 80 W at 25°C Case Temperature
- 10 A Continuous Collector Current
- 15 A Peak Collector Current
- Customer-Specified Selections Available



Pin 2 is in electrical contact with the mounting base.

#### absolute maximum ratings at 25°C case temperature (unless otherwise noted)

RATING	SYMBOL	VALUE	UNIT		
	BD245		55		
Collector omitter voltage $(P_{-} = 100.0)$	BD245A	N	70	v	
Collector-emitter voltage ( $R_{BE} = 100 \Omega$ )	BD245B	VCER	90	v	
	BD245C		115		
	BD245		45		
Collector-emitter voltage ( $I_C = 30 \text{ mA}$ )	BD245A	M	60	V	
	BD245B	V <sub>CEO</sub>	80		
	BD245C		100		
Emitter-base voltage		V <sub>EBO</sub>	5	V	
Continuous collector current		Ι <sub>C</sub>	10	A	
Peak collector current (see Note 1)		I <sub>CM</sub>	15	A	
Continuous base current		I <sub>B</sub>	3	A	
Continuous device dissipation at (or below) 25°C case temperature (see Note 2	)	P <sub>tot</sub>	80	W	
Continuous device dissipation at (or below) 25°C free air temperature (see Note	3)	P <sub>tot</sub>	3	W	
Unclamped inductive load energy (see Note 4)		½LI <sub>C</sub> ²	62.5	mJ	
Operating junction temperature range		Тj	-65 to +150	°C	
Storage temperature range		T <sub>stg</sub>	-65 to +150	°C	
Lead temperature 3.2 mm from case for 10 seconds		ΤL	250	°C	

NOTES: 1. This value applies for  $t_p \leq 0.3$  ms, duty cycle  $\leq 10\%.$ 

2. Derate linearly to 150°C case temperature at the rate of 0.64 W/°C.

3. Derate linearly to 150°C free air temperature at the rate of 24 mW/°C.

4. This rating is based on the capability of the transistor to operate safely in a circuit of: L = 20 mH,  $I_{B(on)}$  = 0.4 A,  $R_{BE}$  = 100  $\Omega$ ,  $V_{BE(off)}$  = 0,  $R_S$  = 0.1  $\Omega$ ,  $V_{CC}$  = 20 V.

## PRODUCT INFORMATION

## BD245, BD245A, BD245B, BD245C NPN SILICON POWER TRANSISTORS



#### electrical characteristics at 25°C case temperature

PARAMETER			TEST CONDITION	IS	MIN	ТҮР	MAX	UNIT
V <sub>(BR)CEO</sub>	Collector-emitter breakdown voltage	I <sub>C</sub> = 30 mA (see Note 5)	I <sub>B</sub> = 0	BD245 BD245A BD245B BD245C	45 60 80 100			V
I <sub>CES</sub>	Collector-emitter cut-off current	$V_{CE} = 55 V$ $V_{CE} = 70 V$ $V_{CE} = 90 V$ $V_{CE} = 115 V$	$V_{BE} = 0$ $V_{BE} = 0$ $V_{BE} = 0$ $V_{BE} = 0$	BD245 BD245A BD245B BD245C			0.4 0.4 0.4 0.4	mA
I <sub>CEO</sub>	Collector cut-off current	$V_{CE} = 30 V$ $V_{CE} = 60 V$	I <sub>B</sub> = 0 I <sub>B</sub> = 0	BD245/245A BD245B/245C			0.7 0.7	mA
I <sub>EBO</sub>	Emitter cut-off current	V <sub>EB</sub> = 5 V	I <sub>C</sub> = 0				1	mA
h <sub>FE</sub>	Forward current transfer ratio	$V_{CE} = 4 V$ $V_{CE} = 4 V$ $V_{CE} = 4 V$	$I_{C} = 1 A$ $I_{C} = 3 A$ $I_{C} = 10 A$	(see Notes 5 and 6)	40 20 4			
V <sub>CE(sat)</sub>	Collector-emitter saturation voltage	$I_{B} = 0.3 A$ $I_{B} = 2.5 A$	$I_{\rm C} = 3$ A $I_{\rm C} = 10$ A	(see Notes 5 and 6)			1 4	V
V <sub>BE</sub>	Base-emitter voltage	$V_{CE} = 4 V$ $V_{CE} = 4 V$	$I_{\rm C} = 3 \text{ A}$ $I_{\rm C} = 10 \text{ A}$	(see Notes 5 and 6)			1.6 3	V
h <sub>fe</sub>	Small signal forward current transfer ratio	V <sub>CE</sub> = 10 V	I <sub>C</sub> = 0.5 A	f = 1 kHz	20			
h <sub>fe</sub>	Small signal forward current transfer ratio	V <sub>CE</sub> = 10 V	I <sub>C</sub> = 0.5 A	f = 1 MHz	3			

NOTES: 5. These parameters must be measured using pulse techniques,  $t_p = 300 \ \mu s$ , duty cycle  $\leq 2\%$ .

6. These parameters must be measured using voltage-sensing contacts, separate from the current carrying contacts.

#### thermal characteristics

PARAMETER	MIN	ТҮР	MAX	UNIT
R <sub>0JC</sub> Junction to case thermal resistance			1.56	°C/W
R <sub>0JA</sub> Junction to free air thermal resistance			42	°C/W

#### resistive-load-switching characteristics at 25°C case temperature

	PARAMETER	TEST CONDITIONS <sup>†</sup>			MIN	ТҮР	МАХ	UNIT
t <sub>on</sub>	Turn-on time	I <sub>C</sub> = 1 A	$I_{B(on)} = 0.1 A$	$I_{B(off)} = -0.1 A$		0.3		μs
t <sub>off</sub>	Turn-off time	$V_{BE(off)} = -3.7 V$	$R_L = 20 \Omega$	$t_p$ = 20 µs, dc $\leq$ 2%		1		μs


<sup>†</sup> Voltage and current values shown are nominal; exact values vary slightly with transistor parameters.






## BD245, BD245A, BD245B, BD245C NPN SILICON POWER TRANSISTORS

## **TYPICAL CHARACTERISTICS**







## PRODUCT INFORMATION

JUNE 1973 - REVISED SEPTEMBER 2002 Specifications are subject to change without notice.

### MAXIMUM SAFE OPERATING REGIONS







PRODUCT INFORMATION