



Features

- Rugged construction



This series is obsolete and not recommended for new designs.

Model C-303™ 5-Pin Non-Protecting Modules

Bourns® Model C-303™ Non-Protecting Modules provide continuity or ground in a 5-pin type protector for use in central office connector, remote and building entrance terminal applications. The housings are made of colored self-extinguishing insulating material. When inserted into the connector sockets, contact pins provide the following connections for each cable pair:


- ground that also acts as a polarization pin
- tip and ring to the outside cable
- tip and ring to the central office equipment

Non-protecting modules are available with gold-plated outside plant and central office pins; the grounding pin is always tin-alloy plated.

- Non-protecting modules with gold-plated pins are intended to be used in connectors with gold-plated protector receptacles.


5-Type Direct Feed Modules

These modules give circuit continuity between the outside plant and central office pairs. Used in locations where protection is not required.



Denied Service Grounding Modules

These green-colored modules are used to temporarily disconnect a subscriber's line. The modules provide a permanent ground on all terminated outside plant cable pairs that are not being used or those that are in an idle condition. This prevents noise induction to the adjacent circuits. There is no connection on the central office equipment pins.



BOURNS®

Asia-Pacific: Tel: +886-2 2562-4117 • Email: asiacus@bourns.com

EMEA: Tel: +36 88 885 877 • Email: eurocus@bourns.com

The Americas: Tel: +1-951 781-5500 • Email: americus@bourns.com

www.bourns.com



WARNING Cancer and Reproductive Harm - www.P65Warnings.ca.gov

Specifications are subject to change without notice.

Users should verify actual device performance in their specific applications.

The products described herein and this document are subject to specific legal disclaimers as set forth on the last page of this document, and at www.bourns.com/docs/legal/disclaimer.pdf.

Model C-303™ 5-Pin Non-Protecting Modules

BOURNS®

How to Order

Product Code	Part Number	Application	Description	Housing Color	Type Number	Pin Plating	Figure Number (see page 3)
5-Type Modules Equipped with Gold-Plated Pins							
*	2400-30-G	Unprotected Circuit	Continuity Module, 1.6 "	Brown	*	Gold	3
*	2400-32-G	Unprotected Circuit	Continuity Module, 1.6 "	Green	*	Gold	3
*	2400-33-G	Unprotected Circuit	Continuity Module, 1.6 "	Red	*	Gold	3
*	2400-35-G	Unprotected Circuit	Continuity Module, 1.6 "	Gray	*	Gold	3
*	2400-310-G	Unprotected Circuit	Continuity Module, 1.6 "	Yellow	*	Gold	3
*	2400-50-G	Unprotected Circuit	Continuity Module, 0.73 "	Brown	*	Gold	1
303M-05A6G0	A0337864	Unprotected Circuit	Continuity Module, 0.73 "	Gray	C-5A1D	Gold	1
303M-05A3G0	A0338073	Special Circuit	Continuity Module, 0.73 "	Red	C-5A3D	Gold	1
303M-05A9G0	A0338075	Reversed Pairs	Continuity Module, 0.73 "	White	C-5A9D	Gold	1
303M-05C6G0	A0334926	Unprotected Circuit	Continuity Module, 2.1 "	Gray	C-4B12C	Gold	2
303M-05F6G0	A0358284	Unprotected Circuit	Continuity Module, 2.1 ", Test Points	Gray	C-4C12C	Gold	2
303M-13D2G0	303M-13D2G0	Service Denied	Grounding Module, 0.73 "	Green	*	Gold	6
303-1053	A0294497	Service Denied	Grounding Module, 1.6 "	Green	*	Gold	4
303-1054	A0294510	Service Denied	Grounding Module, 2.1 "	Green	*	Gold	5
303M-05A2G0	A0338072	Service Denied	Open Module, 0.73 "	Green	C-5A2D	Gold	1

* Pair reversing module: This module identifies and corrects reversed pairs in the outside plant. It is intended for temporary use until the reversed pairs can be rewired correctly.

Notes:

- Order by Part Number.
- Ground pin is tin-plated on all models.

Packaging Specifications

Standard Packaging	200 modules for 5A-type; 100 modules for all others
Dimensions (H x W x D)	8 x 15 x 20 cm (3 x 6 x 8 in.)
Shipping Weight	1.8 kg (4 lb)

Specifications are subject to change without notice.

Users should verify actual device performance in their specific applications.

The products described herein and this document are subject to specific legal disclaimers as set forth on the last page of this document, and at www.bourns.com/docs/legal/disclaimer.pdf.

Model C-303™ 5-Pin Non-Protecting Modules

BOURNS®

Product Dimensions

Figure 1
5A-Type Continuity Module




Figure 2
5F-Type Continuity Module




Figure 3
3A-Type Continuity Module




Figure 4
3A-Size Grounding Module




Figure 5
4A-Size Grounding Module





Figure 6
5A-Size Grounding Module



DIMENSIONS: $\frac{\text{MM}}{(\text{INCHES})}$

REV. L 11/25

Specifications are subject to change without notice.

Users should verify actual device performance in their specific applications.

The products described herein and this document are subject to specific legal disclaimers as set forth on the last page of this document, and at www.bourns.com/docs/legal/disclaimer.pdf.

This legal disclaimer applies to purchasers and users of Bourns® products manufactured by or on behalf of Bourns, Inc. and its affiliates (collectively, "Bourns").

Unless otherwise expressly indicated in writing, Bourns® products and data sheets relating thereto are subject to change without notice. Users should check for and obtain the latest relevant information and verify that such information is current and complete before placing orders for Bourns® products.

The characteristics and parameters of a Bourns® product set forth in its data sheet are based on laboratory conditions, and statements regarding the suitability of products for certain types of applications are based on Bourns' knowledge of typical requirements in generic applications. The characteristics and parameters of a Bourns® product in a user application may vary from the data sheet characteristics and parameters due to (i) the combination of the Bourns® product with other components in the user's application, or (ii) the environment of the user application itself. The characteristics and parameters of a Bourns® product also can and do vary in different applications and actual performance may vary over time. Users should always verify the actual performance of the Bourns® product in their specific devices and applications, and make their own independent judgments regarding the amount of additional test margin to design into their device or application to compensate for differences between laboratory and real world conditions.

Unless Bourns has explicitly designated an individual Bourns® product as meeting the requirements of a particular industry standard (e.g., ISO/TS 16949) or a particular qualification (e.g., UL listed or recognized), Bourns is not responsible for any failure of an individual Bourns® product to meet the requirements of such industry standard or particular qualification. Users of Bourns® products are responsible for ensuring compliance with safety-related requirements and standards applicable to their devices or applications.

Bourns® products are not recommended, authorized or intended for use in nuclear, lifesaving, life-critical or life-sustaining applications, nor in any other applications where failure or malfunction may result in personal injury, death, or severe property or environmental damage. Unless expressly and specifically approved in writing by two authorized Bourns representatives on a case-by-case basis, use of any Bourns® products in such unauthorized applications might not be safe and thus is at the user's sole risk. Life-critical applications include devices identified by the U.S. Food and Drug Administration as Class III devices and generally equivalent classifications outside of the United States.

Bourns expressly identifies those Bourns® standard products that are suitable for use in automotive applications on such products' data sheets in the section entitled "Applications." Unless expressly and specifically approved in writing by two authorized Bourns representatives on a case-by-case basis, use of any other Bourns® standard products in an automotive application might not be safe and thus is not recommended, authorized or intended and is at the user's sole risk. If Bourns expressly identifies a sub-category of automotive application in the data sheet for its standard products (such as infotainment or lighting), such identification means that Bourns has reviewed its standard product and has determined that if such Bourns® standard product is considered for potential use in automotive applications, it should only be used in such sub-category of automotive applications. Any reference to Bourns® standard product in the data sheet as compliant with the AEC-Q standard or "automotive grade" does not by itself mean that Bourns has approved such product for use in an automotive application.

Bourns® standard products are not tested to comply with United States Federal Aviation Administration standards generally or any other generally equivalent governmental organization standard applicable to products designed or manufactured for use in aircraft or space applications. Bourns expressly identifies Bourns® standard products that are suitable for use in aircraft or space applications on such products' data sheets in the section entitled "Applications." Unless expressly and specifically approved in writing by two authorized Bourns representatives on a case-by-case basis, use of any other Bourns® standard product in an aircraft or space application might not be safe and thus is not recommended, authorized or intended and is at the user's sole risk.

The use and level of testing applicable to Bourns® custom products shall be negotiated on a case-by-case basis by Bourns and the user for which such Bourns® custom products are specially designed. Absent a written agreement between Bourns and the user regarding the use and level of such testing, the above provisions applicable to Bourns® standard products shall also apply to such Bourns® custom products.

Users shall not sell, transfer, export or re-export any Bourns® products or technology for use in activities which involve the design, development, production, use or stockpiling of nuclear, chemical or biological weapons or missiles, nor shall they use Bourns® products or technology in any facility which engages in activities relating to such devices. The foregoing restrictions apply to all uses and applications that violate national or international prohibitions, including embargos or international regulations. Further, Bourns® products and Bourns technology and technical data may not under any circumstance be exported or re-exported to countries subject to international sanctions or embargoes. Bourns® products may not, without prior authorization from Bourns and/or the U.S. Government, be resold, transferred, or re-exported to any party not eligible to receive U.S. commodities, software, and technical data.

To the maximum extent permitted by applicable law, Bourns disclaims (i) any and all liability for special, punitive, consequential, incidental or indirect damages or lost revenues or lost profits, and (ii) any and all implied warranties, including implied warranties of fitness for particular purpose, non-infringement and merchantability.

For your convenience, copies of this Legal Disclaimer Notice with German, Spanish, Japanese, Traditional Chinese and Simplified Chinese bilingual versions are available at:

Web Page: <http://www.bourns.com/legal/disclaimers-terms-and-policies>

PDF: <http://www.bourns.com/docs/Legal/disclaimer.pdf>