



# Riedon™ UL Class T and ANL Fuse Blocks by Bourns Product Guide

## Class T Fuse Block

Series	Photo	Fuse Range	Termination	Dielectric Strength	Operating Temperature
CFB		110 - 400 A	Bare Wire	750 VDC	-40 °C to +60 °C
FB		110 - 400 A	Ring/Spade	750 VDC	-40 °C to +60 °C

Clear touch-safe snap-on polycarbonate cover included.

## ANL Fuse Block

Series	Photo	Current Rating	Termination	Dielectric Strength	Operating Junction Temperature
NFB		Max. 500 A	Ring/Spade	750 VDC	-40 °C to +60 °C
NFB2		Max. 500 A	Ring/Spade	750 VDC	-40 °C to +100 °C

Clear touch-safe polycarbonate cover and hardware included.  
Fuse not included.

[www.bourns.com](http://www.bourns.com)

Americas: Tel +1-951 781-5500  
Email [americus@bourns.com](mailto:americus@bourns.com)

EMEA: Tel +36 88 885 877  
Email [eurocus@bourns.com](mailto:eurocus@bourns.com)

**BOURNS®**

Asia-Pacific: Tel +886-2 256 241 17  
Email [asiacus@bourns.com](mailto:asiacus@bourns.com)

Mexico: Tel +52 614 478 0400  
Email [mexicus@bourns.com](mailto:mexicus@bourns.com)