

# **Features**

- Lead free
- RoHS compliant\*
- Multiple isolated resistors
- Stable thin-film-on-silicon technology
- Ultra-miniature packages to JEDEC standards



# **Applications**


- Series bus resistance
- Pull-up/pull-down
- Ideal for space-constrained applications

# Thin Film on Silicon 2QSP / 2NBS -XX1 Isolated Resistors

#### **General Information**

Isolated resistor networks are commonly used in digital circuits where series resistors are required on the system bus. Fabricated with Tantalum Nitride and Nickel Chromium technology on Silicon, these resistors feature excellent stability, TCR and tracking performance. This product series is available in a range of miniature package types conforming to JEDEC standards.

#### **Package Schematic**



#### **Electrical & Environmental Characteristics**

Electrical Characteristics	Symbol	Minimum	Nominal	Maximum	Unit
Resistance Range	R	10		100 K	Ω
Tolerance:					
Absolute		±0.5 %		±5 %	Ω
Ratio		±0.1 %		±2 %	Ω
TCR: Absolute Tracking			100	150 25	ppm/°C ppm/°C
Operating Voltage				50	V
Environmental Characteristics					
ESD		2 K			V
Operating Temperature	TJ	-55		+125	°C
Storage Temperature	T <sub>stg</sub>	-65		+150	°C
Power Rating per Resistor @ 70 °C				0.1	Watt
Power Rating per Package @ 70 °C: QSOP: 16 Pin 20, 24 Pin 28 Pin				0.75 1.00 1.12	Watt Watt Watt
NBSOIC: 8 Pin 14, 16 Pin				0.60 1.00	Watt Watt

<sup>\*</sup>RoHS Directive 2002/95/EC Jan 27, 2003 including Annex


# Thin Film on Silicon 2QSP / 2NBS -XX1 Isolated Resistors


# BOURNS

#### **Mechanical Characteristics**

#### **QSOP Package Dimensions**

# 3.81 - 3.99 (.150 - .157) PIN 1 - .21 - .31 (.008 - .012)







Model	Α			
2QSP16	4.80 - 4.98 (.189196)			
2QSP20	8.56 - 8.74 (.337344)			
2QSP24	8.56 - 8.74 (.337344)			
2QSP28	9.80 - 9.98 (.386393)			


Governing dimensions are in mm. Dimensions in parentheses are in inches and are approximate.

JEDEC Reference Number MO-137.

# Narrow-Body SOIC Package Dimensions







Model	Α			
2NBS08	4.80 - 4.98 (.189196)			
2NBS14	8.56 - 8.74 (.337344)			
2NBS16	9.80 - 9.98 (.386393)			

Governing dimensions are in mm. Dimensions in parentheses are in inches and are approximate.

JEDEC Reference Number MS-012.


# Thin Film on Silicon 2QSP / 2NBS -XX1 Isolated Resistors

# **BOURNS®**


# **QSOP Package Power Temperature Derating Curve**

# 1.25 2QSP28 2QSP24 2QSP16 2QSP16 25 50 75 100 125 150 AMBIENT TEMPERATURE (°C)

# Narrow-Body SOIC Package Power Temperature Derating Curve



#### **Schematic**




# Standard Resistance Values

Resistance (ohms)	Resistance Code
10	100
22	220
33	330
39	390
47	470
51	510
68	680
120	121
220	221
270	271
330	331
470	471
510	511
680	681
1 K	102
2.2 K	222
4.7 K	472
5 K	502
8.2 K	822
10 K	103
18 K	183
20 K	203
47 K	473
50 K	503
100 K	104

#### **Typical Part Marking**

Represents total content. Layout may vary.




# Thin Film on Silicon 2QSP / 2NBS -XX1 Isolated Resistors

# BOURNS®

#### Dispensing

For large quantities, the product will be dispensed in Tape and Reel (see diagram below).



Package	Α <sub>0</sub>	В <sub>0</sub>	κ <sub>0</sub>	Width	Pitch	No. of Pieces per 13 reel	No. of Pieces per tube
QSOP							
16 Pin	6.4 (0.252)	5.2 (0.205)	2.1 (0.083)	12 (0.472)	8 (0.315)	3,500	98
20, 24 Pin	6.5 (0.256)	9.0 (0.354)	2.1 (0.083)	16 (0.630)	8 (0.315)	3,500	56
28 Pin	6.5 (0.256)	10.3 (0.406)	2.1 (0.083)	16 (0.630)	8 (0.315)	3,500	49
NBSOIC							
8 Pin	6.4 (0.252)	9.0 (0.354)	2.1 (0.083)	12 (0.472)	8 (0.315)	3,500	98
14 Pin	6.5 (0.256)	9.0 (0.354)	2.1 (0.083)	16 (0.630)	8 (0.315)	3,500	56
16 Pin	6.5 (0.256)	9.0 (0.354)	2.1 (0.083)	16 (0.630)	8 (0.315)	3,500	49

# Product Class Thin-Film-on-Silicon Standard Package Style QSP = QSOP NBS = Narrow-Body SOIC Pin Count QSP = 16, 20, 24, 28 NBS = 8, 14, 16 Dispensing R = Reel T = Tube Standard Grade Tolerance J = ±5 % G = ±2 % F = ±1 % Circuit 1 = Isolated Resistance Value Code 1st two digits are significant, 3rd digit = number of zeros to follow to give resistance value in ohms. In the standard Grade Tolerance Value Code Is two digits are significant, Is digit = number of zeros to follow to give resistance value in ohms.



Asia-Pacific:

Tel: +886-2 2562-4117 • Fax: +886-2 2562-4116

Europe:

Tel: +41-41 768 5555 • Fax: +41-41 768 5510

The Americas:

Tel: +1-951 781-5500 • Fax: +1-951 781-5700

www.bourns.com