















Bourns® POWrFuse™ High-Power Fuses Product Guide






POWrFuse™ INDUSTRIAL POWER FUSES

Model Series	Mounting Type	Dimensions (mm)	Rated Current	Rated Voltage	Interrupting Rating	Agency Recognition
PF-J	 PCB/T3	10.4 dia. x 38.5	30-70 A	500 VAC 125 VDC	2000 A @ 500 VAC 2000 A @ 250 VAC 1000 A @ 125 VDC	
PF-G	 PCB/T3	14.6 dia. x 38.5	63 A	600 VAC 125 VDC	1500 A @ 600 VAC 2000 A @ 250 VAC 500 A @ 125 VDC	
			90 A	500 VAC	1500 A @ 500 VAC	
PF-H (ind)	 Ferrule/C1	10 dia. x 38	6-12 A	600 VAC 600 VDC	100 kA @ 600 VAC 100 kA @ 600 VDC	
	 PCB/T1					



POWrFuse™ PHOTOVOLTAIC POWER FUSES

Model Series	Mounting Type	Dimensions (mm)	Rated Current	Rated Voltage	Interrupting Rating	Agency Recognition
PF-H (gPV)	 Ferrule/C1	10 dia. x 38	15-30 A	600 VAC 600 VDC	150 kA @ 600 VAC 50 kA @ 600 VDC 10 kA @ 600 VDC	 
	 PCB/T1					
PF-E	 Ferrule/C1	10 dia. x 38	15-30 A	1000 VDC	20 kA @ 1000 VDC	
	 PCB/T1					




POWrFuse™ SEMICONDUCTOR POWER FUSES

Model Series	Mounting Type	Dimensions (mm)	Rated Current	Rated Voltage	Interrupting Rating	Agency Recognition
PF-M	 Bolt/B1	17.2 dia. x 42	50-180 A	240 VAC 150 VDC	160 kA @ 240 VAC 50 kA @ 150 VDC	
PF-F	 Bolt/B1	24.1 dia. x 91.6 35.2 dia. x 95	50-400 A	800 VAC 800 VDC	100 kA @ 800 VAC 50 kA @ 800 VDC	
	 Bolt/B2					

POWrFuse™ EV POWER FUSES*

Model Series	Mounting Type	Dimensions (mm)	Rated Current	Rated Voltage	Interrupting Rating	Qualifications
PF-K	 Bolt/B1	10 dia. x 38	30-50 A	275 VAC 500 VDC	10 kA @ 275 VAC 20 kA @ 500 VDC 10 kA @ 450 VDC	ISO 8820
	 PCB/T1					

POWrFuse™ TELECOM POWER FUSES

Model Series	Mounting Type	Dimensions (mm)	Rated Current	Rated Voltage	Interrupting Rating	Agency Recognition
PF-N	 PCB/T2	14.6 dia. x 22.3	40-80 A	170 VDC	100 kA @ 170 VDC	
	 PCB/T5					

* Meets ISO8820-8 standard