

BOURNS®

- 5 A Continuous On-State Current
- 30 A Surge-Current
- Glass Passivated Wafer
- 400 V to 800 V Off-State Voltage
- Max I_{GT} of 200 μA





Pin 2 is in electrical contact with the mounting base.

absolute maximum ratings over operating case temperature (unless otherwise noted)

RATING			VALUE	UNIT
	TIC106D		400	v
Benetitive peak off state voltage (see Note 1)	TIC106M	M	600	
Repetitive peak off-state voltage (see Note 1)	TIC106S	VDRM	700	
	TIC106N		800	
	TIC106D		400	v
Repetitive peak reverse voltage	TIC106M	V	600	
	TIC106S	VRRM	700	
	TIC106N		800	
Continuous on-state current at (or below) 80°C case temperature (see Note 2)		I _{T(RMS)}	5	А
Average on-state current (180° conduction angle) at (or below) 80°C case temperature			3.2	А
(see Note 3)			0.2	~
Surge on-state current at (or below) 25°C (see Note 4)			30	А
Peak positive gate current (pulse width < 300 µs)		I _{GM}	0.2	А
Peak gate power dissipation (pulse width < 300 µs)		Р _{GM}	1.3	W
Average gate power dissipation (see Note 5)		P _{G(AV)}	0.3	W
Operating case temperature range			-40 to +110	°C
Storage temperature range		T _{stg}	-40 to +125	°C
Lead temperature 1.6 mm from case for 10 seconds		Τ _L	230	°C

NOTES: 1. These values apply when the gate-cathode resistance R_{GK} = 1 k\Omega.

2. These values apply for continuous dc operation with resistive load. Above 80°C derate linearly to zero at 110°C.

3. This value may be applied continuously under single phase 50 Hz half-sine-wave operation with resistive load. Above 80°C derate linearly to zero at 110°C.

4. This value applies for one 50 Hz half-sine-wave when the device is operating at (or below) the rated value of peak reverse voltage and on-state current. Surge may be repeated after the device has returned to original thermal equilibrium.

5. This value applies for a maximum averaging time of 20 ms.

PRODUCT INFORMATION

MDC1ACA

TIC106 SERIES SILICON CONTROLLED RECTIFIERS



electrical characteristics at 25°C case temperature (unless otherwise noted)

	PARAMETER		TEST CONDITIO	NS	MIN	ТҮР	MAX	UNIT
I _{DRM}	Repetitive peak off-state current	V_{D} = rated V_{DRM}	$R_{GK} = 1 \ k\Omega$	T _C = 110°C			400	μA
I _{RRM}	Repetitive peak reverse current	V_{R} = rated V_{RRM}	I _G = 0	T _C = 110°C			1	mA
I _{GT}	Gate trigger current	V _{AA} = 12 V	R _L = 100 Ω	t _{p(g)} ≥ 20 μs		5	200	μA
V _{GT}	Gate trigger voltage	V _{AA} = 12 V t _{p(g)} ≥ 20 μs	R _L = 100 Ω R _{GK} = 1 kΩ	$T_{\rm C} = -40^{\circ}{\rm C}$			1.2	
		V _{AA} = 12 V t _{p(g)} ≥ 20 μs	R _L = 100 Ω R _{GK} = 1 kΩ		0.4	0.6	1	V
		V _{AA} = 12 V t _{p(g)} ≥ 20 μs	R _L = 100 Ω R _{GK} = 1 kΩ	$T_{C} = 110^{\circ}C$	0.2			
Ι _Η	Holding current	$V_{AA} = 12 V$ Initiating I _T = 10 mA	R _{GK} = 1 kΩ	$T_{\rm C} = -40^{\circ}{\rm C}$			8	mA
		V _{AA} = 12 V Initiating I _T = 10 mA	$R_{GK} = 1 \ k\Omega$				5	ШA
V_{T}	Peak on-state voltage	I _T = 5 A	(See Note 6)				1.7	V
dv/dt	Critical rate of rise of off-state voltage	$V_{\rm D}$ = rated $V_{\rm D}$	$R_{GK} = 1 \ k\Omega$	T _C = 110°C		10		V/µs


NOTE 6: This parameter must be measured using pulse techniques, $t_p = 300 \ \mu$ s, duty cycle $\leq 2 \ \%$. Voltage sensing-contacts, separate from the current carrying contacts, are located within 3.2 mm from the device body.

thermal characteristics

PARAMETER	MIN	ТҮР	MAX	UNIT
R _{0JC} Junction to case thermal resistance			3.5	°C/W
R _{0JA} Junction to free air thermal resistance			62.5	°C/W

PRODUCT INFORMATION

THERMAL INFORMATION




PRODUCT INFORMATION

APRIL 1971 - REVISED SEPTEMBER 2002 Specifications are subject to change without notice.

BOURNS®



TYPICAL CHARACTERISTICS



PRODUCT INFORMATION