


- Designed for Complementary Use with TIP135, TIP136 and TIP137
- 70 W at 25°C Case Temperature
- 8 A Continuous Collector Current
- Minimum h_{FE} of 1000 at 4 V, 4 A

! This series is obsolete and not recommended for new designs.



Pin 2 is in electrical contact with the mounting base.

MDTRACA

absolute maximum ratings at 25°C case temperature (unless otherwise noted)

RATING		SYMBOL	VALUE	UNIT
Collector-base voltage ($I_E = 0$)	TIP130	V_{CBO}	60	V
	TIP131	V_{CBO}	80	
	TIP132	V_{CBO}	100	
Collector-emitter voltage ($I_B = 0$)	TIP130	V_{CEO}	60	V
	TIP131	V_{CEO}	80	
	TIP132	V_{CEO}	100	
Emitter-base voltage		V_{EBO}	5	V
Continuous collector current		I_C	8	A
Peak collector current (see Note 1)		I_{CM}	12	A
Continuous base current		I_B	0.3	A
Continuous device dissipation at (or below) 25°C case temperature (see Note 2)		P_{tot}	70	W
Continuous device dissipation at (or below) 25°C free air temperature (see Note 3)		P_{tot}	2	W
Unclamped inductive load energy (see Note 4)		$\frac{1}{2}LI_C^2$	75	mJ
Operating junction temperature range		T_j	-65 to +150	°C
Storage temperature range		T_{stg}	-65 to +150	°C
Lead temperature 3.2 mm from case for 10 seconds		T_L	260	°C

NOTES: 1. This value applies for $t_p \leq 0.3$ ms, duty cycle $\leq 10\%$.

2. Derate linearly to 150°C case temperature at the rate of 0.56 W/°C.

3. Derate linearly to 150°C free air temperature at the rate of 16 mW/°C.

4. This rating is based on the capability of the transistor to operate safely in a circuit of: $L = 20$ mH, $I_{B(on)} = 5$ mA, $R_{BE} = 100$ Ω, $V_{BE(off)} = 0$, $R_S = 0.1$ Ω, $V_{CC} = 20$ V.

PRODUCT INFORMATION

electrical characteristics at 25°C case temperature

PARAMETER	TEST CONDITIONS			MIN	TYP	MAX	UNIT
$V_{(BR)CEO}$ Collector-emitter breakdown voltage	$I_C = 30 \text{ mA}$	$I_B = 0$	(see Note 5)	TIP130 TIP131 TIP132	60 80 100		V
I_{CEO} Collector-emitter cut-off current	$V_{CE} = 30 \text{ V}$	$I_B = 0$		TIP130		0.5	
	$V_{CE} = 40 \text{ V}$	$I_B = 0$		TIP131		0.5	
	$V_{CE} = 50 \text{ V}$	$I_B = 0$		TIP132		0.5	
I_{CBO} Collector cut-off current	$V_{CB} = 60 \text{ V}$	$I_E = 0$		TIP130		0.2	
	$V_{CB} = 80 \text{ V}$	$I_E = 0$		TIP131		0.2	
	$V_{CB} = 100 \text{ V}$	$I_E = 0$		TIP132		0.2	
	$V_{CB} = 60 \text{ V}$	$I_E = 0$	$T_C = 100^\circ\text{C}$	TIP130		1	
	$V_{CB} = 80 \text{ V}$	$I_E = 0$	$T_C = 100^\circ\text{C}$	TIP131		1	
	$V_{CB} = 100 \text{ V}$	$I_E = 0$	$T_C = 100^\circ\text{C}$	TIP132		1	
I_{EBO} Emitter cut-off current	$V_{EB} = 5 \text{ V}$	$I_C = 0$				5	mA
h_{FE} Forward current transfer ratio	$V_{CE} = 4 \text{ V}$	$I_C = 1 \text{ A}$		500			
	$V_{CE} = 4 \text{ V}$	$I_C = 4 \text{ A}$	(see Notes 5 and 6)	1000		15000	
$V_{CE(sat)}$ Collector-emitter saturation voltage	$I_B = 16 \text{ mA}$	$I_C = 4 \text{ A}$	(see Notes 5 and 6)			2	V
	$I_B = 30 \text{ mA}$	$I_C = 6 \text{ A}$				3	
V_{BE} Base-emitter voltage	$V_{CE} = 4 \text{ V}$	$I_C = 4 \text{ A}$	(see Notes 5 and 6)			2.5	V
C_{obo} Output capacitance	$V_{CB} = 10 \text{ V}$	$I_E = 0$				200	pF
V_{EC} Parallel diode forward voltage	$I_E = 8 \text{ A}$	$I_B = 0$	(see Notes 5 and 6)			3.5	V

NOTES: 5. These parameters must be measured using pulse techniques, $t_p = 300 \mu\text{s}$, duty cycle $\leq 2\%$.

6. These parameters must be measured using voltage-sensing contacts, separate from the current carrying contacts.

thermal characteristics

PARAMETER	MIN	TYP	MAX	UNIT
$R_{\theta JC}$ Junction to case thermal resistance			1.78	°C/W
$R_{\theta JA}$ Junction to free air thermal resistance			62.5	°C/W

PRODUCT INFORMATION

JUNE 1973 - REVISED SEPTEMBER 2002

Specifications are subject to change without notice.

TYPICAL CHARACTERISTICS




Figure 1.




Figure 2.




Figure 3.

PRODUCT INFORMATION

JUNE 1973 - REVISED SEPTEMBER 2002

Specifications are subject to change without notice.

MAXIMUM SAFE OPERATING REGIONS




Figure 4.

THERMAL INFORMATION




Figure 5.

PRODUCT INFORMATION